

SUPERTUFF FIBERGLASS TOTE BOX

**Heavy Duty,
Holds Up to 300 lbs.
180° Stacks and Nests**

Stack when filled, turn 180° and nest when empty. These tough reinforced boxes will not rust, corrode, rot or dent and will resist water, oil and most chemicals. FDA approved material. Heat resistant up to 300°F. Stacks 10 high. **300 lb. capacity** per box. Specify color suffix for container, cover and dolly: Gray (GY)✓, Green (GN)✓, Red (RD)✓, White (WH), Blue (BL) or Yellow (YL). Container and cover sold in carton quantities. Dolly sold each.



48 HOUR
48
SHIPMENT ✓

Top Outside L" x W" x H"	Cu. Ft.	Ctn. Qty.	CONTAINER Model	Price Each 10-30 40+	Ctn. Qty.	COVER Model	Price Each 10-30 40+	DOLLY Model	Price Each
17 ⁷ / ₈ x 10 ⁵ / ₈ x 5	.3	10	FD422196	\$12.75 \$11.50	10	FD603071	\$10.75 \$10.00	FD603079	\$59.95
19 ³ / ₄ x 12 ¹ / ₂ x 6	.6	10	FD422198	14.75 13.00	10	FD603072	12.75 11.50	FD603080	65.95
20 ¹ / ₂ x 12 ⁷ / ₈ x 8	.82	10	FD603069	17.50 16.25	10	FD603073	13.25 11.50	FD603081	65.95
24 ¹ / ₄ x 14 ³ / ₄ x 8	1.1	10	FD422202	20.75 18.50	10	FD603074	16.25 15.25	FD603082	66.95
25 ¹ / ₄ x 18 x 6	1.2	6	FD239626	22.75 21.25	6	FD239648	18.50 17.50	FD603083	66.95
25 ¹ / ₄ x 18 x 10	1.8	5	FD422204	27.95 26.95	5	FD603075	18.25 17.50	FD603083	66.95
42 ¹ / ₂ x 20 x 7 ¹ / ₂	2.4	5	FD422207	44.95 41.95	5	FD603076	33.95 31.95	FD603085	102.95
27 ¹ / ₂ x 20 x 14 ¹ / ₈	3.3	5	FD603070	42.95 37.95	5	FD603077	22.50 21.25	FD603084	79.95
42 ¹ / ₂ x 20 x 14 ¹ / ₄	5.4	1	FD422208	53.95 49.95	1	FD603078	33.95 31.95	FD603086	102.95

AS LOW AS
\$11⁵⁰

FIBERGLASS STACKING BOX

Reinforced stackable, polyester fiberglass construction. Ideal for parts handling, transport, etc. 200 lb. capacity per box. Weather and wear resistant. Endures temperature extremes from -40° to +300°. Tight seal lids secure contents. Easy to clean. Add dolly for mobility. Please add color suffix to model number when ordering container and lid: Gray (GY), Green (GN) or White (WH).

Top Outside L" x W" x H"	BOX Model	Cu. Ft.	Price Each 1-11 12+	LID Model	Price Each
6 ¹ / ₈ x 4 ⁷ / ₈ x 2 ¹ / ₈ *	FD114000	.03	\$4.15 \$3.99	FD114030	\$3.55
9 ³ / ₄ x 6 ¹ / ₈ x 2 ¹ / ₈ *	FD114001	.06	6.50 6.20	FD114031	5.20
9 ³ / ₄ x 9 ¹ / ₄ x 2 ¹ / ₈ *	FD114002	.09	7.80 7.50	FD114032	5.40
12 ³ / ₈ x 9 ³ / ₄ x 2 ¹ / ₈ *	FD114003	.12	9.20 8.90	FD114033	6.90
9 ³ / ₄ x 6 ¹ / ₈ x 4 ¹ / ₂ *	FD114004	.12	8.20 7.80	FD114034	5.20
18 ³ / ₄ x 11 ⁷ / ₈ x 1 ³ / ₄	FD603091	.18	12.75 12.00	---	---
9 ³ / ₄ x 9 ¹ / ₄ x 4 ¹ / ₂ *	FD114005	.20	9.50 9.00	FD114035	5.50
11 ³ / ₄ x 8 ³ / ₄ x 4 ¹ / ₈ *	FD114006	.19	9.80 9.50	FD114036	6.90
14 ³ / ₈ x 14 ³ / ₈ x 3 ¹ / ₂	FD603092	.33	17.75 17.25	---	---
16 ¹ / ₂ x 11 ³ / ₈ x 4 ⁵ / ₈	FD603093	.38	15.75 15.25	---	---
22 x 12 x 1 ¹ / ₄	FD603095	.18	11.50 11.00	---	---
23 ³ / ₈ x 12 x 3 ¹ / ₈	FD603096	.42	15.50 14.75	---	---
23 ³ / ₈ x 12 x 6	FD603097	.83	26.95 25.95	---	---
25 ³ / ₄ x 17 ³ / ₄ x 3	FD114007	.63	21.50 21.00	FD114037	20.00
25 ³ / ₄ x 17 ³ / ₄ x 4 ¹ / ₂	FD114008	.95	23.50 22.75	FD114038	19.75
25 ³ / ₄ x 17 ³ / ₄ x 6	FD114009	1.27	27.95 26.95	FD114039	19.75

AS LOW AS
\$3⁹⁹



OPTIONAL DOLLY BASE-
4 swivel 3" hard rubber wheel
casters. Gray color.
25³/₄ x 17³/₄.
Model FD114040 \$75.95

* Stackable with lid only.

FIBERGLASS HOPPER BIN

Nest and also provide positive lockstacking. Ideal for heavy parts storage. Fiberglass reinforced bins hold up to **500 lbs. capacity**. Withstands temperatures from -60° F to 300° F and autoclaving. Resists most oils, moisture, solvents and chemicals. Front label area accommodates adhesive labels. Add color suffix to model number when ordering: Green (GN), Gray (GY) or Red (RD).

AS LOW AS
\$19⁵⁰

**500 lb.
Capacity**



Model	Top Outside L" x W"	Top Inside L" x W"	Height"	Ctn. Qty.	Price Each 1-5 Ctns. 6+ Ctns.
FD257817	18 x 11 ¹ / ₂	16 x 8	7 ¹ / ₂	10	\$20.50 \$19.50
FD257818	24 x 11 ¹ / ₂	21 ¹ / ₂ x 9	8	10	24.50 23.50
FD257819	24 x 16 ¹ / ₂	22 x 13	5	5	30.95 29.95

NESTABLE SHIPPING CONTAINERS

Made using injection-molded high density polyethylene, reusable for over 250 trips. Molded-in grip handles with integral hasp accept cable ties or padlocks. Nestable when empty for reduced return shipping costs. Gray color. **Optional Lids** (sold separately) allow secure stacking with raised lip edges. Sold in carton quantities of 5.

AS LOW AS
\$13²⁵



Model	Top Outside L" x W" x H"	Package Cu. Ft. Qty.	Price Each 1-20 21+	LID Model	Price Each 1-20 21+
FD269303	21 x 15 ¹ / ₈ x 5 ¹ / ₈	0.8 5	\$13.75 \$13.25	FD269309	\$6.20 \$5.90
FD269304	21 ¹³ / ₁₆ x 15 ³ / ₁₆ x 9 ⁹ / ₁₆	1.4 5	14.50 13.75	FD269310	6.20 5.90
FD269305	21 ³ / ₈ x 15 ⁵ / ₁₆ x 12 ⁵ / ₁₆	2.0 5	15.50 14.75	FD269309	6.20 5.90
FD269306	21 ⁷ / ₈ x 19 ⁵ / ₈ x 12	2.7 5	21.75 20.75	FD269311	8.00 7.70
FD269302	21 ⁵ / ₈ x 13 ³ / ₁₆ x 11	1.3 5	22.50 21.50	FD269308	8.50 8.20
FD269307	28 x 20 ⁵ / ₈ x 12	3.2 5	25.75 21.75	---	---

1-800-645-1232

globalindustrial.com

19