

NEST & STACK SHIPPING TOTE

Made with injection molded, high density polyethylene to withstand extreme temperatures from -10°F to 250°F. Complies with **USDA** and **FDA** regulations for use in food processing applications. Totes won't crack or corrode and are waterproof. 180 degree nest and stacking saves valuable storage space. Fits on standard 48" x 40" pallets. Features a textured bottom to ensure a non-slip grip during transport. **Optional Lid** protects contents and accepts security tie closure for added security. Sold in carton quantities. Specify color suffix: **Blue (BL)**, **Gray (GY)** or **Red (RD)**.

**180° Turn
Allows
Stack & Nest**

AS LOW AS
\$6.20

Top Outside L" x W" x H"	Lbs. Cap		Ctn. Qty.	TOTE Model	Price Each	LID Model	Price Each
	Per Box	Stacked					
18 x 11 x 6	45	225	6	FD274311	\$6.20	FD274321	\$4.46
18 x 11 x 9	90	450	6	FD274312	8.10	FD274321	4.46
19 1/2 x 13 1/2 x 8	65	325	6	FD274313	10.75	FD274322	6.50
19 1/2 x 15 1/2 x 10	55	275	6	FD274314	12.25	FD274323	5.90
19 1/2 x 15 1/2 x 13	65	325	6	FD274315	12.50	FD274323	5.90
23 1/2 x 15 1/2 x 12	90	450	3	FD274316	16.50	FD274324	9.30
23 1/2 x 19 1/2 x 10	45	225	6	FD274317	15.25	FD274325	8.80
23 1/2 x 19 1/2 x 13	75	375	3	FD274318	18.50	FD274325	12.75
29 1/2 x 19 1/2 x 15	100	500	3	FD274319	30.95	FD274326	12.75



Model	Description	Price
FD274320	3" x 5" Label Holder (Pkg of 6)	\$8.30
FD239893	Security Cable Tie (Pkg of 375)	8.95
FD239894	Plastic Dolly, 1000 lb. cap. ID 24"L x 16 3/4"W, OD 30"L x 18"W	88.95

48 HOUR
48
SHIPMENT



NEST & STACK SHIPPING TOTE

USDA approved injection molded, high density polyethylene provides strength that complies with **FDA** regulations for use in food processing. Lids easily snap-on to protect contents. Quick 180° turn offers space saving stacking and nesting. Stacks up to 6 high. Fits 48" x 40" pallets. withstands temperatures from -10°F to 150°F. Sold in carton quantities. Specify color suffix: **Blue (BL)**, **Gray (GY)** or **Red (RD)**.

48 HOUR
48
SHIPMENT

Top Outside L" x W" x H"	Cu. Ft.	Lbs. Cap		Ctn. Qty.	TOTE Model	Price Each	LID Model	Price Each
		Per Box	Stacked					
18 x 11 x 6	0.50	45	225	6	FD498403	\$7.90	FD498401	\$5.40
18 x 11 x 9	0.76	90	450	6	FD752431	10.00	FD498401	5.40
19 1/2 x 13 1/2 x 8	0.80	65	325	6	FD498830	13.25	FD498832	8.10
19 1/2 x 15 1/2 x 10	1.20	55	275	6	FD498422	15.00	FD498420	7.40
19 1/2 x 15 1/2 x 13	1.73	65	325	6	FD752430	16.50	FD498420	7.40
23 1/2 x 15 1/2 x 12	1.70	90	450	3	FD498831	20.50	FD498833	11.25
23 1/2 x 19 1/2 x 10	2.00	45	225	6	FD752429	18.50	FD498425	10.75
23 1/2 x 19 1/2 x 13	2.60	75	375	3	FD498427	22.75	FD498425	10.75
29 1/2 x 19 1/2 x 15	3.70	100	500	3	FD498464	38.95	FD498467	15.50

FD239430 3 3/4" x 5" clear plastic label holder (pkg. of 6) \$9.20

STEEL DOLLIES
900 lbs. cap. 3" Poly casters.

Model	Fits Container	Price
FD652812	29 1/2"L x 19 1/2"W	\$69.95
FD652813	23 1/2"L x 19 1/2"W	64.95
FD652814	23 1/2"L x 15 1/2"W	61.95



POLYETHYLENE CONTAINER Nest & Stack



AS LOW AS
\$11.50



SAME DAY
**IN
STOCK**
SHIPMENT

Designed to endure years of rugged use in manufacturing, food processing, distribution and storage. High density polyethylene resists oils, solvents, most chemicals and steam and withstands 0°-120°F. Blue and Grey containers are **FDA approved** for direct food contact. Reinforced construction provides 70 lb. capacity per container. Bottom container supports 300 lbs. when stacked. Nest when empty, cross stack without lids or stack with lids. Add color suffix: **Red (RD)**, **Blue (BL)** or **Gray (GY)**.

Top Outside L" x W" x H"	Cu. Ft.	Ctn. Qty.	CONTAINER		LID Model	Price Each
			Model	Price Each		
20 x 13 x 6 1/4	0.6	5	FD652905	\$12.50	FD652911	\$7.20
21 x 17 x 12	1.8	5	FD652906	20.50	FD652912	7.90
24 x 14 x 8	1.1	5	FD652907	17.25	FD652913	7.40
24 x 20 x 13	2.7	5	FD652908	23.00	FD652914	10.00
26 x 18 3/4 x 10	2.1	10	FD652909	25.00	FD652915	9.40
30 x 24 x 15	4.7	---	FD652910	40.95	----	----



NEST AND STACK PALLET CONTAINER



Integrated 180° stack and nest system for compact storage and transport on 40 x 48 pallets. Ideal for food processing, general manufacturing, work-in-process handling, merchandise distribution and more. Solid walls and sides for a leak-proof interior that is easy to clean. Label areas for content identification. Handles for easy lifting. **Optional Lid** protects contents and allows stacking. Gray color. **Plastic Dolly** allows mobility of stacked containers.

Top Outside L" x W" x H"	Cu. Ft.	Ctn. Qty.	Price Each	
			Model	1-20 21+
23 5/8 x 15 3/4 x 5 1/4	0.8	5	FD443115	\$17.50 \$16.75
23 5/8 x 15 3/4 x 7 1/8	1.0	5	FD443116	19.00 17.75
23 5/8 x 15 3/4 x 8 1/2	1.3	5	FD443117	20.00 18.75
23 5/8 x 15 3/4 x 10 3/4	1.6	5	FD443118	22.25 20.75
23 5/8 x 15 3/4 x 14 1/4	2.1	5	FD443119	26.95 25.95
Lid for 23 5/8"L x 15 3/4"W footprint container		5	FD443120	9.20 8.70
Plastic Dolly 2 Swivel 2 Rigid			FD443121	59.95 ---