

# DELINEATOR POST

Ideal for directing vehicular and pedestrian traffic. Meets MUTCD standards. All models, **except Style B**, are available with reflective strips for high visibility at night. **Style A** features a grab handle top for easy lifting and accepts barrier tape. Orange 4" diameter post includes detachable 12 lb. base. **Styles B & C** are made of high density polyethylene and include a base that allows floor anchoring. **Style B** measures 5" diameter x 42"H. **Style C** can be weighted with sand to stand on its own and measures 5 3/4" diameter. Available in 3 colors. **Specify Color Suffix: Orange (RG), Lime (LVI) or Yellow (YL).** **Style D** features a unique angled handle with molded-in holes that accept **Flashing Light**, traffic signs, or barrier tape. Orange 4" diameter post allows nesting when not in use and accepts Recycled **Rubber Base** for stability.



AS LOW AS  
**\$14.95**

Description	Model	42" POST Price Each		28" POST Price Each	
		1-5	6+	1-5	6+
<b>A.</b> Solid Orange Post	FD116122	\$17.95	\$16.95	FD116119	\$15.95
<b>A.</b> Reflective Post	FD116123	20.95	19.95	FD116120	18.95
<b>B.</b> Solid Yellow Post	FD442635	24.99	23.45		
<b>C.</b> Reflective Post	FD652955	38.75	35.75		
<b>D.</b> Reflective Post	FD238874	15.95	15.35		
16 lbs. Rubber Base for Style D				FD238875	11.50
Flashing Light for Style D				FD238876	22.50

# TRAFFIC CONES

Meet MUTCD Standards!

Tough, weatherproof orange PVC Traffic Cones have a tip-resistant, weighted base. 18" cones have one 6" reflective collar; 28" and 36" cones have a 6" and a 4" reflective collar. Meets MUTCD standards. Sold in package quantities. **Custom Cone Imprinting** - Simply supply your vertical or horizontal typed message on white paper and it will be sized to fit. Black imprinting on one side. **50 cone minimum order.** Add C suffix to cone model number and \$0.50 per cone to price.



AS LOW AS  
**\$6.99**

SAME DAY IN STOCK SHIPMENT

H" x Sq."	Wt.	Ctn. Qty.	A. NON REFLECTIVE Price Each			B. REFLECTIVE Price Each				
			1 ctn.	2-3 ctn.	4+ ctn.	1 ctn.	2-3 ctn.	4+ ctn.		
18 x 11 1/2	3lb.	20	FD337005	\$7.59	\$7.35	\$6.99	FD116125	\$11.45	\$11.20	\$10.80
28 x 13	5lb.	10	FD337006	11.40	10.95	10.35	FD116126	17.20	16.95	16.30
28 x 15 1/2	7lb.	8	FD337200	14.25	13.95	13.35	FD337202	21.79	21.25	20.40
28 x 15 1/2	10lb.	6	FD337201	18.65	18.15	17.50	FD337203	24.45	24.00	23.15
36 x 15 1/2	10lb.	4	FD337008	18.85	18.35	17.65	FD116127	25.25	24.60	23.65

## TRAFFIC CONE HOLDERS

Holds ten 18" cones or five 28" cones. 22" H. Vertical Mount Horizontal Mount Price/Pack of 2  
**Vertical Mount** is ideal for bumpers or back of trucks. **Horizontal Mount** designed for bumpers, flatbeds or compartment tops.

FD238244	FD238245	\$26.95
----------	----------	---------

# INTERLOCKING SAFETY BARRICADE



AS LOW AS  
**\$132**

Direct traffic flow or cordon off hazards or construction with these forkliftable, high density polyethylene barricades. Dovetail joints interlock and stay together securely. **Sections can be filled with water or sand up to 400 lbs.** and include cable lugs for joining to prevent theft. Visibility is enhanced with reflective strips. **Specify color suffix: Orange (RG), White (WH) or Yellow (YL).**

Model	L" x W" x H"	Price Each		
		1-3	4-6	7+
FD652837	72 x 16 x 35	\$269.95	\$259.95	\$252.95
FD238277	60 x 16 x 24	147.95	139.95	132.00

For use in narrow walkways, hallways, driveways, sidewalks and more. Stackable for transport and storage. NCHRP 350 compliant. Federal Highway Administration Approved. Measures 13"W x 3"D when folded. **Barricade with Sheeting** includes two 12" x 24" engineer grade reflective striped sheets. **Blank Barricade** allows easy installation of your choice of Legend (sold separately). Barricades sold in packages of 2. **Add Color Suffix: White (WH), Yellow (YL) or Orange (RG).**

# FOLDING BARRICADES/ SIGN STANDS



Model	Description	H"	Price Each	
			1-4	6+
FD442380	Two Sheatings	45	\$46.50	\$42.50
FD442381	Two Sheatings	36	42.50	38.50
FD268622	No Sheeting	45	33.50	30.50
FD268623	No Sheeting	36	29.50	27.50
	Engineer Grade Legend*		9.25	8.50

Model* Legend	FD268624 SLOW	FD268630 STOP	FD268629 PARKING LOT CLOSED	FD268625 PARKING w/Left Arrow
Model* Legend	FD268626 PARKING w/Right Arrow		FD268627 KEEP LEFT w/Arrow	FD268628 KEEP RIGHT w/Arrow

# PLASTIC SAFETY DRUMS

Constructed from tough, resilient high density plastic to bounce back after repeated impacts. Meets NCHRP requirement 350. All models include four 4" reflective sheeting bands in choice of economical Engineered grade or High Intensity grade. Bases sold separately. Choose from 25 lbs. Rubber Base, Standard Base (for sand bag use) or sand fill bases. 18" diam. x 36"H.

Model	Description	Price Each	
		1-3	4+
FD442375	Drum with Engineer Sheeting and Tire Ring Base	\$38.95	\$35.95
FD238246	Drum with Engineer Sheeting	45.29	\$41.00
FD238247	Drum with High Intensity Sheeting	62.95	58.95
FD238248	Standard Base	7.60	7.25
FD238249	Sand Fillable Base	12.30	11.50
FD239202	Rubber Base	19.95	18.25
FD442382	Flashing Light	22.50	20.50



RUBBER BASE

# FOLDING TRAFFIC BARRICADES



AS LOW AS  
**\$35**

Model	H"	Panel W" x L"	Panel Qty.	Sheeting Side	Price Each	
					1-3	4+
<b>A. ECONOMIC</b>						
FD442376	40	8 1/2 x 72	1	2	\$59.95	\$55.95
FD442377	40	8 1/2 x 72	2	4	89.95	82.95
<b>B. PREMIUM</b>						
FD940385	42	7 1/2 x 72	1	2	76.50	73.25
FD940386	42	7 1/2 x 72	2	4	119.95	109.95
FD940387	42	7 1/2 x 96	1	2	89.95	84.95
FD940388	42	7 1/2 x 96	2	4	145.95	135.95
<b>C. PORTABLE</b>						
FD442378	42 3/8	8 x 24	4	2	38.50	35.00
FD442379	42 3/8	8 x 24	4	4	45.50	41.50

Easy to store and set up to direct traffic or limit access indoors or outdoors. **Economic & Premium** include A-frame polyethylene legs. Beams include high visibility reflective engineer grade sheets on both sides. **Economy** includes 3/4" thick plastic Type III boards. **Premium** features unique 1 1/8" thick plastic I-Beam boards that assures rigidity and protects sheeting. Meets MUTC standards. **Portable** feature engineer grade reflective sheeting on both sides for safety.