

# ALL WELDED STACKABLE STEEL CONTAINER



STANDARD SOLID WALL CONTAINER



STANDARD WIRE MESH CONTAINER

AS LOW AS  
**\$162**

Quality engineered for the toughest industrial uses. Includes 3/16" thick 2" angle corners and unique corner pockets to permit positive stacking up to five high. Heavy duty stacking legs with convenient 4" under clearance allow four way accessibility for easy fork or pallet truck handling. **SOLID WALL** has 13 gauge corrugated sides for strength and rigidity; 4000 lb. capacity. **WIRE MESH** feature 3/16" wire mesh sides for air circulation; 2500 lb. capacity. Must specify hopper front or drop gate option suffix below or standard fixed wall container will be shipped. **Specify color suffix and add \$40.00 to price or unpainted will be shipped: Dark Blue (B), Teal Green (G), Black (BK) or Gray (GY).**

**Stacks 5 High**

18" HIGH I.D. SOLID WALL				24" HIGH I.D. SOLID WALL				24" HIGH I.D. WIRE MESH			
L" x W"	Model	Price		Model	Price	Model	Price	Model	Price	Model	Price
30 x 24	FD800199	\$162.00		FD800101	\$198.95	---	---	---	---	---	---
30 x 30	---	---		FD800100	211.95	---	---	---	---	---	---
35 x 30	---	---		FD800102	214.95	---	---	---	---	---	---
35 x 35	FD800204	205.95		FD800104	229.95	FD800105	\$277.95	FD800111	295.95	---	---
42 x 30	FD800206	208.95		FD800106	242.95	---	---	FD800113	317.95	---	---
42 x 35	FD800210	219.95		FD800110	252.95	---	---	FD800115	359.95	---	---
48 x 35	FD800212	244.95		FD800112	269.95	---	---	FD800117	375.95	---	---
42 x 42	FD800214	264.95		FD800114	279.95	---	---	FD800119	386.95	---	---
48 x 42	FD800216	279.95		FD800116	305.95	---	---	---	---	---	---
48 x 48	FD800218	288.95		FD800118	325.95	---	---	---	---	---	---

FD800110GJ  
SHOWN WITH OPTIONAL HOPPER FRONT

FD800106GYM  
SHOWN WITH OPTIONAL DROP GATE

**HOPPER FRONT/DROP GATE OPTION**  
Available on 24"H x 35", 42" or 48"W containers only. If container has 2 sides with these widths, specify the side on which opening is desired. Otherwise, opening will be placed on longest side by default. To order: First add a color suffix. Second add the door type suffix from below, choosing the compatible side type (solid or mesh) to match the container desired. Be sure to add the option price, as well. Example: Model 800116GYM is a Gray, solid wall container with the door located on the 48"W side.

	Door Suffix	Price
<b>Hopper Front (Solid Only)</b>	J	\$60.00
<b>Drop Gate Solid Wall</b>	M	40.00
<b>Wire Mesh</b>	S	55.00

## NESTABLE PLASTIC STORAGE CONTAINERS

AS LOW AS  
**\$299**



*Nestable, Stackable And Forkliftable To Handle All Jobs!*



Constructed of 1/4" thick polyethylene for corrosion and impact resistance. Nests when empty, stackable with included lid. Rib reinforced sidewalls for added strength. **2-Way Forklift Access** features rib reinforced base for added strength. **4-Way Forklift Access** features smooth interior base surface. **2-Way Forkliftable Containers** available with 5" swivel casters and steel dumping bracket base with fork pockets. **Specify Color Suffix: Blue (BL), Green (GN), Gray (GY), Red (RD) or FDA approved Natural (WH).**

Outside L" x W" x H"	Inside H"	Cap. Cu. ft.	Lbs.	Fork Entry	CONTAINER W/ LID		CONTAINER W/LID DUMPING BRACKET & CASTERS	
					Model	Price	Model	Price
44 x 44 x 32 1/2	27	32	700	2	FD442350	\$299.00	FD442356	\$445.00
44 x 44 x 44	37	38	800	2	FD442351	354.00	FD442357	499.00
48 x 48 x 30	29	32	1500	2	FD442352	379.00	FD442358	525.00
48 x 48 x 46	43	40	1500	2	FD442353	435.00	FD442359	579.00
45 x 50 x 36	28 7/10	30	2000	4	FD442354	545.00	---	---
45 x 50 x 39	31 1/2	32	2000	4	FD442355	555.00	---	---

## STACKING PALLET CONTAINER



AS LOW AS  
**\$245**

FD652756GY

FD652757BL

Ideal for agricultural, pharmaceutical, industrial and food service use, these high grade, **USDA approved** high density polyethylene structural foam containers resist rust, chemicals, rotting and warping, and withstand temperatures from 0°-140°F. 4-way fork entry. Stack 10 high with interlocking corners. Caster models have 6" plate casters (2 swivel, 2 rigid) and stack with reinforced dolly base. Available with solid or vented sides, long side runners or short side runners. **Vented container Gray only. Add color suffix: Gray (GY), Blue (BL) or White (WH) for solid container.**

	SOLID	VENTED	Price	Style	O.D. L" x W" x H"	Cap. Lbs.	Stacking Cap.Lbs.
<b>LONG SIDE RUNNERS</b>							
	FD652755	FD652756	\$245.00	w/o Casters	48 x 40 x 31	1500	14000
	FD652757	FD652758	\$19.00	w/Casters	48 x 40 x 31	1500	14000
<b>SHORT SIDE RUNNERS</b>							
	FD442743	FD442744	245.00	Container	48 x 40 x 31	1500	14000