



# CLIPPER® HI-PERFORMANCE® INDUSTRIAL SHELVING

Unique, industrial grade shelving is easily adjusted and re-adjusted while maintaining rigid strength. Box beam reinforced shelves are height adjustable at 1" increments on strong steel upright posts. **Open Shelving** includes anti-sway bracing and allows access on all sides. **Closed Shelving** includes side and back panels to prevent items from falling. Gray powder coat finish.

**Starter Units** includes 2 box and 2 angle posts. 5 shelves and cross braces or panels.

**Add-On Units** includes 1 box and 2 angle posts. 5 shelves and cross braces or panels.



**BOX POSTS, USED AT FRONT OF UNIT, ALLOW FULL-WIDTH ACCESS TO SHELVES. SHELF CLIPS ENGAGE POSTS AT FOUR POINTS AND KEEPS SHELF SNUGLY IN PLACE.**

AS LOW AS  
**\$99**



**CLOSED SHELVING**



**OPEN SHELVING**

AS LOW AS  
**\$48**  
SHIPMENT

W" x D" x H"	Cap. Lbs.	Model	STARTER		ADD-ON	
			Price Each 1-7	8+	Model	Price Each 1-7 8+
<b>OPEN SHELVING</b>						
36 x 12 x 87	800	FD652102✓	\$107.95	\$99.00	FD652114✓	\$91.95 \$86.95
36 x 18 x 87	800	FD652103✓	121.95	114.95	FD652115✓	104.95 99.95
36 x 24 x 87	800	FD652104✓	134.95	127.95	FD652116✓	118.95 112.95
48 x 12 x 87	500	FD652105	124.95	117.95	FD652117	108.95 102.95
48 x 18 x 87	500	FD652106	153.95	144.95	FD652118	137.95 129.95
48 x 24 x 87	500	FD652107✓	174.95	164.95	FD652119✓	158.95 149.95
<b>CLOSED SHELVING</b>						
36 x 12 x 87	800	FD652108✓	147.95	139.95	FD652120✓	124.95 117.95
36 x 18 x 87	800	FD652109✓	169.95	159.95	FD652121✓	142.95 134.95
36 x 24 x 87	800	FD652110✓	191.95	179.95	FD652122✓	159.95 149.95
48 x 12 x 87	500	FD652111	179.95	169.95	FD652123	158.95 149.95
48 x 18 x 87	500	FD652112	217.95	204.95	FD652124	189.95 179.95
48 x 24 x 87	500	FD652113✓	247.95	233.95	FD652125✓	214.95 202.95

**ADDITIONAL SHELVES**

Model	Price Each 1-7	8+
FD652126✓	\$12.25	\$11.75
FD652127✓	15.25	14.50
FD652128✓	18.00	17.00
FD652129	16.00	15.25
FD652130	22.00	20.75
FD652131✓	27.95	26.95

## LYON SHELVING

Great for storage of heavy duty items such as wheels, gears, sprockets, etc. Durable shelving uses steel shelves with lapped and welded shelf corners for increased strength. Features a unique box W-configuration for increased rigidity. Patented roll formed steel T-post uprights allow easy shelf height adjustments at 1 1/2" increments. Includes hardware for installation. **Open Shelving** allows high visibility of stored packaged stock or other materials. **Closed Shelving** shields packages and unboxed items from dust, contaminants and sunlight.

**Open Starter Units** include 4 posts, 5 shelves, rear braces and 2 side braces. **Open Add-On** includes 2 posts, 5 shelves, rear and side braces. **Closed Starter Units** includes 4 posts, 5 shelves, back panel and 2 side panels. **Closed Add-On** includes 2 posts, 5 shelves, one back and one side panel. **Closed Panels** are welded to the T-Posts for increased strength. **Specify color suffix: Gray (GY) or Putty (PY).**



**OPEN SHELVING**



**Shelf Clip.** Firmly locks shelf to upright without tools.



**T-Post.** Formed steel with punching.

AS LOW AS  
**\$209**

W" x D" x H Level	Cap. Lbs./	Model	STARTER		ADD-ON		ADDITIONAL SHELVES	
			Price Ea. 1-7	8+	Model	Price Ea. 1-7	Model	Price Ea. 1-7
<b>OPEN SHELVING</b>								
36 x 12 x 84	800	FD580173	\$209.00	FD580182	\$169.95	FD580809	\$24.95	
36 x 18 x 84	900	FD580174	244.95	FD580183	196.95	FD580810	29.95	
36 x 24 x 84	800	FD580175	279.95	FD580184	229.95	FD580811	38.95	
48 x 12 x 84	600	FD580176	247.95	FD580185	199.95	FD580812	34.95	
48 x 18 x 84	600	FD580177	287.95	FD580186	239.95	FD580813	46.95	
48 x 24 x 84	560	FD580178	327.95	FD580187	277.95	FD580814	56.95	
<b>CLOSED SHELVING</b>								
36 x 12 x 84	800	FD580191	293.95	FD580800	229.95	FD580809	24.95	
36 x 18 x 84	900	FD580192	327.95	FD580801	259.95	FD580810	29.95	
36 x 24 x 84	800	FD580193	371.95	FD580802	298.95	FD580811	38.95	
48 x 12 x 84	600	FD580194	339.95	FD580803	277.95	FD580812	34.95	
48 x 18 x 84	600	FD580195	386.95	FD580804	319.95	FD580813	46.95	
48 x 24 x 84	560	FD580196	436.95	FD580805	362.95	FD580814	56.95	

Additional Lyon Shelving Available Online at [globalindustrial.com](http://globalindustrial.com)

## IMPERIAL SHELVING

High Density Filing

AS LOW AS  
**\$219**

Unique design saves up to 60% floor space compared to conventional filing. Helps make files more visible and accessible. Double walled T-post uprights feature welded steel panels, shoulder rivets and shelf supports to withstand up to 400 lb. shelf capacity. Steel shelves are height adjustable at 1 1/2" increments. 12" and 15" depth units include 5 large 10 1/2"D x 7 1/2"H adjustable dividers per shelf that adjust along the backstop at 2" increments. 24" and 30" depth units include 10 dividers per shelf. Non-marring molded polyethylene floor caps protects floors and carpets. Easy assembly. Enamel sand finish.



W" x D"	Model	Price
<b>REFERENCE SHELF</b>		
30 x 12	FD962632	\$28.95
30 x 15	FD962633	29.95
30 x 24	FD962648	31.95
30 x 30	FD962649	32.95

W" x D" x H	Openings	Model	Price	STARTER		ADDITIONAL SHELVES	
				Model	Price	Model	Price
36 x 12 x 76	6	FD962600	\$219.00	FD962642	\$201.95	FD962634	\$22.95
48 x 12 x 76	6	FD962601	269.95	FD962643	244.95	FD962635	29.95
36 x 15 x 76	6	FD962602	249.95	FD962644	221.95	FD962636	24.95
36 x 12 x 88	7	FD962603	253.95	FD962645	228.95	FD962634	22.95
48 x 12 x 88	7	FD962604	298.95	FD962646	272.95	FD962635	29.95
36 x 15 x 88	7	FD962605	275.95	FD962647	248.95	FD962636	24.95
<b>DOUBLE SIDE ACCESS</b>							
36 x 24 x 76	6	FD962606	401.95	FD962618	380.95	FD962654	42.95
48 x 24 x 76	6	FD962607	487.95	FD962619	461.95	FD962655	53.95
36 x 30 x 76	6	FD962608	461.95	FD962620	441.95	FD962656	46.95
36 x 24 x 88	7	FD962609	457.95	FD962621	438.95	FD962654	42.95
48 x 24 x 88	7	FD962610	552.95	FD962622	535.95	FD962655	53.95
36 x 30 x 88	7	FD962611	491.95	FD962623	457.95	FD962656	46.95