



## PARAMOUNT® CLEAR VIEW CABINET



4" BARREL HINGES



REINFORCED DOORS

AS LOW AS  
**\$299<sup>95</sup>**

SAME DAY  
**IN STOCK**  
SHIPMENT

**The best storage cabinet value on the market.** Rugged door construction, where it matters most! Extra large 4" x 3/8" barrel hinges (3 per door). Channel reinforced impact resistant acrylic windows, 3-point locking system with pry-resistant solid steel 5/16" rods, dual chrome plated die-cast key locking handles. **Meets ANSI/BIFMA shelf capacity standards.** Box-formed 36" W shelves have full width steel channel reinforcement (two on 48"W) to help prevent shelf deflection. **Holds 300 lbs. per shelf.** 48"W cabinet includes center I-beam installed in the base of the cabinet. Tough, scratch-resistant powder coat finish. \*Available in Gray and Tan only. **Assembled cabinets are non-returnable.** Add color suffix: Black (BK), Tan (TN) or Gray (GY).

W" x D" x H"	Openings/ Adj. Shelves	Description	Model	Price Each		ADDITIONAL SHELVES	
				1-2	3+	Model	Price/ Pkg. 2
36 x 18 x 78	5/4	Easy Assembly	FD237614*	\$329.95	\$299.95	FD237580	\$33.95
36 x 18 x 78	5/4	Assembled	FD237620*	369.95	339.95	FD237652	33.95
48 x 24 x 78	5/4	Easy Assembly	FD237615	489.95	439.95	FD237581	68.95
48 x 24 x 78	5/4	Assembled	FD237621	569.95	519.95	FD237653	68.95



## CLEAR-VIEW CABINETS

AS LOW AS  
**\$265**

All Welded

High impact acrylic windows provide visibility. 36"W cabinets have 180 lb. shelf capacity. 46"W have 230 lb. shelf capacity. Shelves adjust on 2" centers. Bottom shelf is fixed. **Meets ANSI/BIFMA shelf capacity standards.** 2 chrome handles with 3-point locking system secures doors. **All welded steel construction** and powder coat finish ensure long lasting service. **Mobile cabinet** comes with patented caster base with 4 durable 5" diameter swivel casters (2 locking). **Available in Black (BK), Light Gray (LG), Putty (PY) or Sand (SD).** Shipped assembled.

FULL HEIGHT  
FD198686PY

W" x D" x H"	Openings/ Adj. Shelves	STATIONARY Model	Price Each		MOBILE Model	Price Each	
			1-2	3+		1-2	3+
36 x 12 x 42	3/2	FD240446	\$286.95	\$265.00	---	---	---
36 x 18 x 42	3/2	FD198685	295.95	278.95	FD603063	\$411.95	\$388.95
36 x 24 x 42	3/2	FD603062	332.95	312.95	FD603064	455.95	429.95
36 x 12 x 72	5/4	FD240447	375.95	352.95	---	---	---
36 x 18 x 72	5/4	FD198686	395.95	372.95	FD603065	516.00	487.95
36 x 24 x 72	5/4	FD198687	425.95	396.95	FD603066	554.00	524.00
46 x 18 x 42	3/2	FD198688	375.95	356.95	FD603067	485.95	457.95
46 x 24 x 42	3/2	FD240448	402.95	378.95	FD240449	527.00	498.95
46 x 18 x 72	5/4	FD198689	502.00	469.95	FD603068	632.00	596.00
46 x 24 x 72	5/4	FD237673	592.00	554.00	FD237674	699.00	659.00

## "THE ORGANIZER" HEAVY DUTY CABINET



FD603314

All Welded

SAME DAY  
**IN STOCK**  
SHIPMENT



38" CABINET  
HASP



48" CABINET  
HASP

Assembled 16 gauge steel cabinets are finished in gray baked enamel and have 4 adjustable shelves. Pegboard panel on each door provides room for an array of equipment. Includes padlock hasp, leveling feet and assorted pegboard hooks...create a system that works with your equipment.

Model	W" x D" x H"	Description	Shelf Cap.	Price
FD500336	38 x 24 x 72	60 Pegboard Hooks	800 lb.	\$775.00
FD603314	48 x 24 x 72	90 Pegboard Hooks	700 lb.	999.00
FD336375P		Padlock with 2 Keys		3.50



## SLIDING DOOR STORAGE CABINET

Provides A Safe, Attractive  
Storage Solution

Easy-to-open sliding doors provide a neat, attractive appearance that's ideal for contemporary office environments. Simply slide doors to side for easy access to half of cabinet. Sliding doors come with die cast pull handles and Cam lock. Made with heavy gauge furniture quality steel. Height adjustable shelves adjust at 2" increments and have a capacity of **150 lbs. per shelf.** Cylinder locks with 2 keys for security. Powder coat finish. **Specify color suffix: Black (BK), Gray (GY) or Tan (TN).**

FD237786GY

AS LOW AS  
**\$209**

W" x D" x H"	Openings/ Adj. Shelves	Model	Price Each	
			1-2	3+
36 x 12 x 30	2/1	FD237782	\$225.95	\$209.00
36 x 18 x 30	2/1	FD237783	249.95	236.95
36 x 12 x 42	3/2	FD237784	255.95	239.95
36 x 18 x 42	3/2	FD237785	268.95	252.95
36 x 12 x 72	5/4	FD237786	318.95	299.95
36 x 18 x 72	5/4	FD237787	327.95	305.95