



AS LOW AS
\$399

PORTABLE INDUSTRIAL GENERATORS

Make these reliable, efficient portable generators part of your hurricane and disaster preparation today. Air-cooled systems powered by dependable unleaded gasoline engines protected with low oil shut down guard and circuit breaker protection. **Honda Engine Models** are housed in a roll cage for strength and protection during transport. **Generac Engine Models** have hardened steel-tube cradle with folding handles and never-flat wheels. **Generator sales are final.**



Model	Surge Watts	Rated Watts	HP	Engine	Starting System	Tank Gal. Cap.	Run Time/Hrs. Half Load	Panel Outlet	Price Each	
HS249462	3,750	3,250	5.4	Generac OHV	Recoil	4.0	12.5	(4) 5-20R 120V	\$399.00	
HS239109*	2,800	2,500	5	Honda GC 160	Re-coil	0.55	1.1	120v Duplex	499.00	
HS249464	6,875	5,500	13	Generac OHV	Recoil	6.6	10	(4) 5-20R 120V; (1) L14-30R twist-lock 120/240V	644.00	
HS249465	8,000	6,500	13	Generac OHV	Recoil	6.6	10	(4) 5-20R 120V; (1) L14-30R twist-lock 120/240V	744.00	
HS249470	8,750	7,000	13.6	Generac OHVI	Electric/Recoil	8.0	11	(4) 5-20R 120V; (1) L14-30R twist-lock 120/240V	1,048.00	
HS249472	10,000	8,000	13.6	Generac OHVI	Electric/Recoil	8.0	11	(4) 5-20R 120V; (1) L14-30R twist-lock 120/240V	1,147.00	
HS294391*	12,000	10,200	20	Honda GX 620	Electric	8.0	5.6	(2) 120v Duplex, 120/240V TL, 240V TL	1,999.00	
HS606967	10"	Pneumatic Wheel Kit and Sky Hook Kit for Models HS294391 and HS239109								159.00
HS249499	Rechargeable Battery-12 Volt, 18 Amp for Model HS294391									49.95

* Run Time/Hrs. Full Load



HS249462

INDUSTRIAL PRESSURE WASHERS

Gas powered, industrial strength pressure washers available with either a steel frame with a durable powder coat finish or corrosion resistant stainless steel frame. All units feature Comet pump, 10" pneumatic wheels (13" on model HS607719), steel braided hose, 4 spray nozzles, 36" insulated lance, spray gun and chemical injector kit. 9 and 13 HP units feature "oil guard" automatic shut down thermal relief protection. 5 year pump, 2 year engine warranty on Honda GX models.

powered by
HONDA!



Quiet
Running!

Model	Engine	PSI	HP	Gal./Min	Start System	Price
STEEL FRAME w/ POWDER COAT FINISH						
HS190287	Honda GC	2500	5	2.3	Re-Coil	\$458.95
HS607752	Honda GC	2700	6.0	2.5	Re-Coil	534.00
HS294518	Honda GX	2000	5.5	3.0	Re-Coil	712.00
HS294519	Honda GX	2500	6.5	3.0	Re-Coil	814.00
HS294520	Honda GX	3000	9	3.0	Re-Coil	1124.00
HS294521	Honda GX	4000	13	4.0	Re-Coil	1187.00
HS294522	Honda GX	4000	13	4.0	Electric	1374.00
STAINLESS STEEL FRAME						
HS634173	Honda GX	2500	6.5	3.0	Re-Coil	919.00
HS607719	Honda GX	4000	13	3.5	Re-Coil	1322.00

ACCESSORIES

Description	Model	Price
16" WATER BROOM with 4 nozzles - 4 Gal/Min.	HS190304	\$43.95
TELESCOPING WAND 18 FT. for hard to reach areas.	HS190305	119.95
ROTARY NOZZLE 3000 PSI Boosts cleaning impact up to 85%.	HS190306	32.95
Fits all models up to 3000 PSI.		
NOZZLE 4 PACK # 030 - 0°, 15°, 40°, & Soaper.	HS190307	\$19.95
For use with 5 - 6.5 HP models		
NOZZLE 4 PACK # 040 - 0°, 15°, 40°, & Soaper.	HS190308	19.95
For use with 9 HP models and higher.		
50 FT. HOSE WITH COUPLERS	HS190309	79.95
4000 PSI GUN WITH INSULATED LANCE	HS190310	35.95

SURFACE CLEANERS clean large surfaces easily and evenly with up to 4,000 PSI rotary arm and nylon brush skirt. Minimum of 3000 PSI recommended.

Model	Description	Price
HS607735	16" High Density Polyethylene Surface Cleaner	\$274.95
HS607737	20" Stainless Steel Surface Cleaner	539.00



Visit
www.globalindustrial.com
for hundreds of additional
Generators, Pressure Washers
& Pumps

JET ELECTRIC CHAIN HOIST

Heavy duty 115V/230V single phase ventilated motor offers 19.7 fpm lift speed. Thermal overload protection and permanently lubricated gear trains for long life. Electromagnetic brake holds load even if power is interrupted and features slip clutch overload protection. Upper/lower limit switches prevent over-travel. Drop forged hooks swivel 360 degrees for easy rigging. Control cord is 2' shorter than lift. H3 rated. 2 Year Warranty.



HS251429

INCLUDES CHAIN CONTAINER!



INDUSTRIAL WATER AND TRASH PUMPS

Powered by reliable gas engines with automatic low oil shut down guard. Heavy duty self-priming pumps. Corrosive resistant seals. Durable cast iron impellers on all models.



HS300846

Model	Intake/Outlet Diameter"	Engine	HP	GPM	Max. Head'	Max. Draw'	Max. Solid Size"	Price
HS674001	2	Robbins	5.5	141	58	25	N/A	268.00
HS300843	2	Honda GX	4.0	150	105	26	5/16	523.00
HS300844	2	Honda GC	5.0	150	105	26	N/A	436.95
HS300846	3	Honda GX	5.5	265	105	26	5/16	574.00
HS300848	4	Honda GX	11.0	506	95	26	1/4	1,643.00

25' Intake Suction Hose		25' Outlet Discharge Hose		50' Outlet Discharge Hose	
Model	Diameter"	Price	Model	Diameter"	Price
HS300906	2	5.70	HS300895	2	64.95
HS300907	3	6.90	HS300896	3	112.95
HS300908	4	9.20	HS300897	4	153.95

*Order one each for suction and discharge hose



AS LOW AS
\$109

2 year warranty

RETRACTABLE REELS WITH HOSE

Model	W" x D" x H"	Hose' I.D."	Price
COMPOSITE REELS (Spring Rewind)			
HS854100	5 3/4 x 16 1/2 x 17 5/8	25 1/4	\$109.00
HS854104	5 3/4 x 16 1/2 x 17 5/8	50 1/4	164.95
HS854106	5 3/4 x 16 1/2 x 17 5/8	25 3/8	127.95
HS854109	6 1/4 x 16 1/2 x 17 5/8	50 3/8	187.95
HS854112	6 1/4 x 16 1/2 x 17 5/8	25 1/2	176.95
HS854116	6 1/4 x 16 1/2 x 17 5/8	50 1/2	232.95
ALL STEEL COMPACT REELS (Spring Rewind)			
HS237025	5 3/8 x 12 5/8 x 12 1/8	35 1/4	174.95
HS237028	6 x 13 1/2 x 14 1/2	35 3/8	218.95
HS237029	6 x 16 1/2 x 17 1/2	50 3/8	259.95
ALL STEEL REELS (Spring Rewind)			
HS854111	7 x 19 x 20 1/4	50 1/2	311.95
HS854115	10 1/2 x 24 x 25 3/8	100 1/2	469.95

Composite Reels Air and water. Withstand up to 150°F and 300 psi (HS854122 is 250 psi). Base and mount, are heavy gauge reinforced steel with powder coat finish. Corrosion resistant latch mechanism and stainless steel spring. Adjustable guide arm permits floor or wall mount at 7 different angles. **All Steel Full Size & Compact Hose Reels** have same applications, ratings and features as above but with robust steel reel and extra reinforcements for high-demand use.

Model	Cap Lbs.	Lift H'	Motor HP	Head Room"	Price
HS251429	1000	10	7/8	20 3/16	\$1189.00
HS251430	1000	15	7/8	20 3/16	1269.00
HS251431	1000	20	7/8	20 3/16	1299.00
HS251432	2000	10	1 3/4	24 7/16	1459.00
HS251433	2000	15	1 3/4	24 7/16	1499.00
HS251434	2000	20	1 3/4	24 7/16	1569.00