






CL25AE Evaporative Air Cooler

INDOOR USE ONLY

The CL25AE is a great for spot cooling in any home or office. Honeywell evaporative coolers do not require power hungry components like compressors. The CL25AE consumes only 235 watts of power. This low power consumption translates into significant savings on energy bills compared to using air conditioners. Four fan speeds and oscillating louvers improve air circulation and provide an even distribution of cool air for rooms up to 300 square feet.

This unit is lightweight and has side handles and four durable caster wheels allowing easy mobility from room to room.

FEATURES

-  Cools up to 300 Sq.ft (28 Sq. m)*
-  Power consumption 235 Watts
-  Powerful air flow 500 CFM (850 m³/hr)*
-  Water tank capacity 6.6 Gallons (25 Liters)
-  0.5 to 7.5 hours OFF timer
-  Low water alarm
-  3 Speeds control High / Medium / Low
-  Top loading ice compartment
-  Works on inverter
-  Remote control
-  Honeycomb cooling media and carbon-dust filter
-  Easy mobility
-  Oscillating louvers
-  Adjustable humidification level

*All specifications mentioned are under test conditions



CONTROL PANEL



TECHNICAL INFORMATION

| | |
|-------------------------|----------------------------|
| Product Dimensions (in) | 18.9 (L) 14.6 (W) 33.3 (H) |
| Net Weight | 25.4 lbs / 11.5 kg |
| UPC Barcode | 848987000589 |
| EAN Barcode | 4895007930377 |
| Container Qty 40' HQ | 360 pcs |

JMA North America LLC
 Mahwah, New Jersey 07495 USA
 Phone: 1-800-474-2147
 Email: info@jmana.us
 Web: www.honeywellportableac.com

© 2014 AirTek Int'l Corp. Ltd. All rights reserved.
 The Honeywell Trademark is used under license from Honeywell International Inc.
 Honeywell International Inc. makes no representations or warranties with respect to this product.
 This product is manufactured by Airtek Int'l Corp. Ltd.

Honeywell