



RemGrit CARBIDE GRIT HOLE SAWS

Cuts extremely hard abrasive materials: Laminates, fiberglass, ceramic tile, marble, slate, cast iron and composites. Cutting edge of tungsten carbide particles bonded to alloy steel back. High heat and abrasion resistance, no teeth to dull or chip, resists snagging, smooth cutting, greater wear resistance. Ideal for plumbing, construction, marine and aircraft applications.



3/16" (5 mm) thick heavy-duty backing plate eliminates drive hole elongation and the need for drive plate

1-7/16" (37 mm) depth of cut

RemGrit hole saws (without arbors) feature a gulletted grit edge



Boxed

DIAMETER		MODEL #	PRODUCT CODE
INCHES	MM		
5/8	16	G010M	E0206026
3/4	19	G012	E0206001
--	20	G013M	E0206027
7/8	22	G014	E0206002
1	25	G016	E0206003
1-1/8	29	G018	E0206004
1-1/4	32	G020	E0206005
1-3/8	35	G022	E0206006
1-1/2	38	G024	E0206007
1-3/4	44	G028	E0206008
1-7/8	48	G030	E0206023
2	51	G032	E0206009
2-1/8	54	G034	E0206010
2-1/4	57	G036	E0206011
2-3/8	60	G038	E0206024
2-1/2	64	G040	E0206022
2-3/4	70	G044	E0206013
3	76	G048	E0206014
3-1/4	83	G052	E0206015
3-3/8	86	G054	E0206016
3-3/4	95	G060	E0206025
4	102	G064	E0206017
4-1/2	114	G072	E0206018

RemGrit arbored hole saws feature a continuous grit edge

1/4" quick change shank

7/8" (22 mm) depth of cut



Arbored Hole Saws (Clamshelled)

DIAMETER		MODEL#	MIN. ORDER QTY.	PRODUCT CODE
INCHES	MM			
1	25	OGC16BL	2	E0104577
1-1/4	32	OGC20BL	2	E0104578
1-1/2	38	OGC24BL	2	E0104579
1-3/4	44	OGC28BL	2	E0104580
2	51	OGC32BL	2	E0104581
2-1/8	54	OGC34BL	2	E0104582
2-1/4	57	OGC36BL	2	E0104583
2-1/2	64	OGC40BL	2	E0104584



CARBIDE GRIT RECESSED LIGHT INSTALLATION KITS



Complete kits for any recessed light installation job. The carbide grit cutting edge easily cuts through ceiling tile and drywall. Recessed light kits are available for 4", 5" and 6" lighting fixtures.

*Features a
continuous grit
edge*



*Mandrel & Pilot
bit included*

Recessed Light Installation Hole Saws

DIAMETER		MODEL #	PRODUCT CODE
INCHES	MM		
4-3/8	111	GRL402	E0101680
5-3/8	137	GRL502	E0101681
6-3/8	162	GRL602	E0101682

