Cruiser X4 Wheelchair

Lightweight, Dual-Axle Wheelchair







drive			wheelchairs		
Item #	Seat Width	Product Overall Width Open	Armrest	UOM	
CX416ADDA-ELR	16"	23"	Height Adjustable Flip-Back Desk Arm	1/ea	
CX416ADDA-SF	16"	23"	Height Adjustable Flip-Back Desk Arm	1/ea	
CX416ADFA-ELR	16"	23"	Height Adjustable Flip-Back Full Arm	1/ea	
CX416ADFA-SF	16"	23"	Height Adjustable Flip-Back Full Arm	1/ea	
CX418ADDA-ELR	18"	25"	Height Adjustable Flip-Back Desk Arm	1/ea	
CX418ADDA-SF	18"	25"	Height Adjustable Flip-Back Desk Arm	1/ea	
CX418ADFA-ELR	18"	25"	Height Adjustable Flip-Back Full Arm	1/ea	
CX418ADFA-SF	18"	25"	Height Adjustable Flip-Back Full Arm	1/ea	
CX420ADDA-ELR	20"	27"	Height Adjustable Flip-Back Desk Arm	1/ea	
CX420ADDA-SF	20"	27"	Height Adjustable Flip-Back Desk Arm	1/ea	
CX420ADFA-ELR	20"	27"	Height Adjustable Flip-Back Full Arm	1/ea	
CX420ADFA-SF	20"	27"	Height Adjustable Flip-Back Full Arm	1/ea	

- Weighs 34 pounds or less when properly equipped in the basic configuration (Excluding front rigging).
- Easy to propel and transport.
- Frame style eliminates seat guides and allows for custom backs and accessories.
- Flip-back, removable arm is height adjustable from top of seat rail 10" to 14" and features a front mounted easy to use lever release mechanism. (Figure A C)
- Padded armrests provide added patient comfort.
- Height adjustable segmented back.
- Aluminum and Carbon steel blended frame with combination powder coated and silver vein finish is attractive, chip resistant and easy to maintain.
- Durable, flame retardant nylon upholstery resists mildew and bacteria.
- Patented adjustable depth seat. 16" and 18" on chair depths. (Figure D F)
- 3 position quick release rear axles mounted on Composite Mag-style wheels with composite hand rims are lightweight and maintenance free. (Figure G).
- Polyurethane rear tires and composite casters offer superior performance, smoother ride and are lightweight.
- Dual over center cross links provide added rigidity. (Figure H)
- Comes with swing-away footrests or elevating legrests with tool-free adjustable length riggings.
- Composite footplates with heel loops are durable and lightweight.
- Precision sealed wheel bearings through-out ensure long lasting and reliability.
- 8" front casters have 3 height adjustments and angle adjustments. (Figure I)
- Triple rear axle positions provides easy transition of seat height from standard to hemi level.
- Comes with push-to-lock wheel locks.

specifications			
Width Open with 16" 18" 20" Seat	23" 25" 27"	Length with Riggings	43"
Width Closed	12"	Product Weight without Riggings (16", 18", 2	20") 32 lbs. 34 lbs. 36 lbs.
Height	36"	Carton Shipping Weight (16", 18", 20")	46 lbs. 48 lbs. 50 lbs.
Seat-to-Floor Height	17" 18" 19"	Weight Limit	300 lbs.
Back Height	16" - 17.5"	Warranty on Frame	Limited Lifetime
Seat Depth	16"/18" On Chair	Warranty	Limited Lifetime

accessories

Universal Forward Stabilizer			Anti-Fold Bar			
STDS860	Universal Forward Stabilizer		STDS806	Anti-Fold Bar	1/ea	
Anti-Tippers			Wheelchair Cane/ Crutch Holder			
STDS819	Anti-Tippers With Wheels		STDS1034	Wheelchair Cane/Crutch Holder	1/ea	
Seat Belts			Heel Loops			
STDS850	Seat Belts, Auto-Clasp Type Closure	1/ea	STDS831	Heel Loops	1/bx	
STDS851	Seat Belts, Hook and Loop Fastener Type Closure 1/ea		Limb Support			
STDS855	Seat Belts, Auto-Clasp Type Closure, Bariatric	1/ea	WASR	Limb Support, Right	1/ea	
STDS856	Seat Belts, Hook and Loop Fastener Type	1/ea	WASL	Limb Support, Left	1/ea	
	Closure, Bariatric		Chart Carry Pocket			
Wheel Lock Extension		STDS835	Chart Carry Pocket	1/ea		
STDS601	Wheel Lock Extension	1/ea				