

VBS-1610, 16" VERTICAL BANDSAW

414485

The line of JET Vertical Bandsaws offers machine and fabrication professionals all the power and precision in a package that meets their individual specifications. An exclusive gear box design permits variety of cutting applications. Features you've come to expect, backed by the industry-leading JET Two Year Warranty



FEATURES

- Heavy-duty, completely enclosed steel frame
- Multi-tilting worktable
- Easy to read blade tension indicator
- Variable speeds provide proper adjustments for high efficiency cutting
- Bi-Metal blade welder, grinder and cutter
- Worklamp
- Chip blower
- Blade and tire cleaning brush
- Set of tools
- 1/4" x 14/18VT Bi-Metal blade



JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

VBS-1610, 16" VERTICAL BANDSAW

414485

SPECIFICATIONS

Blade Speeds (SFPM)	82 - 3,950
Height Capacity (Max.) (In.)	10
Throat Capacity (In.)	15-1/2
Table Size (L x W) (In.)	22 x 24
Table Tilt (Deg.)	8 F & B, 12 L & 15 R
Blade Length (In.)	123-1/2
Blade Width (Min.-Max.) (In.)	1/8 - 5/8
Table Height (In.)	40
Motor (HP)	2 HP, 230/460V, 3Ph
Overall Dimensions (L x W x H) (In.)	37 x 28 x 72-1/2
Weight (Lbs.)	944



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE