# **MOBILE APP BASED WIRELESS SECURITY ALARM SYSTEM**

The **IWATCHALARM** is a new generation app based do-it-vourself wireless security alarm system. Remote access controls made easy and affordable; no monthly fee and free mobile app. Check on device status, receive alarm alert with push technology, remotely arm and disarm with your Smartphone and tablet. The IWATCHALARM will notify all members who have the app installed with alarm activity sent directly to their phone whenever the alarm system tripped. Above all, optional add-on app based cameras (fixed and pan-tilt) and wall socket can be integrated to optimize your security solution. Monitor, access, and take command of your home automation devices at your finger tip made possible by SecurityMan.



IWATCHALARM (starter kit)

**IWATCHALARMD (Deluxe kit)** 

**IWATCHALARMP (Pro kit)** 

## Installation as easy as 1,2,3

The QR code automatically sets up your host quickly and easily

**Download the Free App** (Apple or Android)



**Connect the Host** & Scan the QR Code



Take control of your security system



**Detect & Monitor** 













#### ADD-ON CAMERAS & WALL SOCKET (Optional)







Pan-Tilt WiFi/Eth Camera SM-821DTH

WiFi Fixed Camera SM-825DTH

Wall Socket Home automation SM-001SK

#### **Features:**

- Mobile App based (Apple/Android) enabled D.I.Y Wireless Security Alarm System
- Real time security breach push notifications
- Self monitored and self controlled; no monthly fees and no contracts
- Full control of your home security from your Smartphone or tablet
- Backup rechargeable battery (up to 6 hrs of standby time)
- Upgradable by adding up to 64 wireless devices; Sensors, Cameras, Sirens, Wall Sockets
- On-Demand video and audio streaming anytime, anywhere. (Requires add-on camera)

#### **Package Contents**

#### **IWATCHALARM**

- 1x Host
- 1x Door/Window Sensor
- 1x Motion Sensor
- 1x Ethernet Cable
- 1x AC Adapter
- Mounting Accessories
- Mounting Accessories
- Quick Start Guide
- User's Manual

#### **IWATCHALARMD**

- 1x Host
- 1x Door/Window Sensor
- 1x Motion Sensor
- 1x Keychain Remote
- 1x Siren (indoor)
- 1x Ethernet Cable
- 2x AC Adapters
- Mounting Accessories
- · Quick Start Guide
- User's Manual

#### **IWATCHALARMD**

- 1x Host
- 2x Door/Window Sensor
- 2x Motion Sensor
- 1x Keychain Remote
- 1x Siren (indoor)
- 1x Ethernet Cable
- 2x AC Adapters
- Mounting Accessories
- · Quick Start Guide
- User's Manual

#### **Key Specifications:**

SM-025H	Power	DC5V 1.0A
Alarm Host	Backup Battery	Built-in Lithium (up to 6 hours standby time)
	Network	WiFi or Ethernet
	Transmission Frequency	433MHz
	Host Buttons	[Top] Arm, Disarm, Power
		[bottom] On/Off switch, Reset, AP (access point)
	LED's (red)	Power, Arm, Pair
	Ports	Power, Ethernet
	Antennas	1 x WiFi (left), 1 x 433MHz wireless (right)
	Size (LxWxH)	6.75" x 4.25" x 1.0"

SM-007R	Battery Powered	DC 3V (CR2032 Lithium battery included, last up to 1 year)
Remote Control	LED's	Red
	Transmission Frequency	433Mhz
	Transmission Distance	up to 150ft with walls, 300ft clear line of sight
	Buttons	Arm, Disarm, Pair, Panic
	Size (LxWxH)	2.75" x 1.63" x .56"
SM-002M	Battery Powered	1.5V (1 x AA battery included, last up to 1 year)
Door/Window Sensor	Pair Button	1 inside (remove cover to pair)
	LED's	Red
	Transmission Frequency	433Mhz
	Magnetic/Emitting Gap	Within 3/8" (1cm)
	Size (LxWxH)	3.0" × 2.0" × .75"
	Transmission Distance	up to 200ft with walls, 450ft clear line of sight
SM-003P	Battery Powered	3.0V (2 x AAA batteries included, last up to 1 year)
PIR Motion Sensor	Pair Button	1 inside (remove cover to pair)
	LED's	Blue
	Low battery	Flashing LED
	Transmission Frequency	433Mhz
	Detecting range	up to 30ft
	Detecting Angle	110 Degrees
	Size (LxWxH)	4.25" x 2.5" x 1.75"
	Transmission Distance	up to 200ft with walls, 450ft clear line of sight
SM-005SR	Power	DC 12V 1.5A
Indoor Siren	Battery Compartment	Yes (uses 3 x AA batteries for backup only, not included)
	Button	Pair
	LED's	Red (4x)
	Transmission Frequency	433Mhz
	Alarm sound	100dB
	Size (LxWxH)	5.5" x 5.5" x 2.0"
	Transmission Distance	up to 150ft with walls, 300ft clear line of sight
IWATCHALARM	Weight gross/net	2.7lb/1.9lb
IWACTHALARMD	Weight gross/net (lb)	3.4lb/2.6lb
IWATCHALARMP	Weight gross/net (lb)	3.8lb/2.9lb

### ADD-ON (Optional):

SM-001SK	Power Input	AC100-240V
Wall Socket	Power Output	Less than 10A
	Button	1 (power on/off, pair)
	LED's	Red
	Transmission Frequency	433MHz
	Size (LxWxH)	4.25" x 2.5" x 1.38"
	Transmission Distance	up to 200ft with walls, 450ft clear line of sight
	Weight gross/net	1.5lb/1.2lb
SM-825DTH	Lens	1/4 " CMOS color
WiFi Fixed IP Camera	Sensor	OV9712
	Focal Length	3.6mm
	Viewing Angle	70 degree
	System	P2P (Cloud Technology)
	Video Compression	H.264

	Resolution	720P HD (1280 x 720)
	Video Rate	30fps
	Motion Detection	Yes
	Transmission	Wi-Fi
	WiFi Interface	802.11b/g/n
	WiFi Frequency	2400-2483.5MHz
	WiFi Channel	11
	LED's	Blue
	Night Vision	Up to 33ft (9pcs IR)
	IR-Cut Filter	Yes
	Two-Way Audio	Yes (built-in Mic and speaker)
	Micro SD Slot	Yes, (supports up to 32GB class 6 or higher/ MicroSD not included)
	Application	iOS, Android
	Buttons	AP (access point mode), Reset
	Light Sensor	Yes
	Size (LxWxH)	4.75" × 2.5" × 1.13"
	Power	DC 5V 1.0A
	Weight gross/net	1.6lb/1.2lb
	Lens	1/4 " CMOS color
SM-821DTH	Sensor	OV9712
Pan-Tilt WiFi/Eth IP	Focal Length	3.6mm
Camera	Pan-Tilt Control	260:Horizontal 120:Vertical (no zoom)
	Viewing Angle	50 degree
	System	P2P (Cloud Technology)
	Video Compression	H.264
	Resolution	720P HD (1280x720), VGA (640x480), QVGA (320x240)
	Video Rate	30fps
	Motion Detection	Yes
	Transmission	Wired Ethernet or Wi-Fi
	NIC Interface	10/100Mbps (IEEE802.3, RJ45)
	Protocols	TCP/IP, DHCP, SMTP,HTTP, UPNP
	WiFi Interface	802.11b/g/n
	WiFi Frequency	2400-2483.5MHz
	WiFi Channel	11
	Speech Mode	12.2kbps (ARM), 8kbps (PCM)
	Two-Way Audio	Yes (built-in Mic and speaker)
	Micro SD Slot	Yes, (supports up to 32GB class 6 or higher/ MicroSD not included)
	Application	iOS, Android
	Playback	Yes
	Users	7 users max
	Security	2 password access control
	Buttons	Pair, Reset
	LED's	Red
	Night Vision	Up to 33ft (11pcs IR)
	IR-Cut Filter	Yes
	Light Sensor	Yes
	Size (LxWxH)	4.5" x 4.0" x 5.5"
	Power Consumption	Max 5W (IR On, WiFi enabled)
	Power	DC 5V 1.2A
	Weight gross/net	2.2lb/1.7lb
SM-105DB	Battery Powered	3V (2 x AAA batteries included, last up to 1 year)
Doorbell	LED's	Red
	Transmission Frequency	433MHz
	Button	1
	Size (LxWxH)	2.94" x 1.56" x .81"
	Transmission Distance	up to 150ft with walls, 300ft clear line of sight