PRODUCT SPECIFICATIONS



Contractor 20' SRL

#727620

Features

- · Rugged, lightweight design. Full inertial brake mechanism.
- · Load-indicating swivel carabiner with 3,600 lb. gate.
- · Rated for one worker up to 310 lbs.
- Meets ANSI Z359.1-2007, ANSI A10.32 and applicable OSHA requirements.

Material Specifications

Cable: 3/16", 7X19 galvanized steel

Connector: Alloy Steel; Min. 5,000 lbs. tensile strength

Connector Gates: Alloy Steel; Min. 3,600 lbs. front load and

side load

Performance Specifications

Tensile Strength: Min. 5,000 lbs. **Max. Capacity:** 310 lbs.

Relevant Standards

OSHA: *CFR1926.502, CFR1910.66*

ANSI: *A10.32-2004*

Warnings

- · Read, understand and follow all labels and instructions prior to use.
- · Inspect before each use.
- · Remove from service if there is evidence of damage or excessive wear.
- · Never attach a Restraint Lanyard to the front or side D-Rings.



FallTech 1306 S. Alameda St. Compton, CA 90221 Tele: 323-752-0066 www.falltech.com