# FRIGIDAIRE.

# Home Comfort



# **Signature Features**

### Effortless<sup>™</sup> Remote Temperature Control

Remote control thermostat precisely maintains preset room temperature, so you can remain comfortable at all times.

## Programmable 24-Hour On/Off Timer

With the 24-Hour On/Off Timer, you can ensure your home will be cool and comfortable when you want it to be without having to worry about running up your utility bills. The built-in timer allows you to preset the unit to turn on and off in half-hour increments.

# **Energy Saver Mode**

Reduce your utility bills in this mode. It cools similarly to central air, with the unit turning on and off at different intervals to ensure the room temperature stays at the set temperature.

## **Multi-Speed Fan**

Features three different fan speeds, for more cooling flexibility.

# Heavy-Duty Air Conditioner

#### **Product Dimensions**

Height	18-5/8″
Width	26-1/2"
Depth	26-1/2"

#### More Easy-To-Use Features

#### Sleep Mode

With Sleep Mode, the temperature gradually increases a few degrees over the evening, saving energy and creating a comfortable environment during the evening hours.

#### **Remote Control**

Offers you the flexibility to control the temperature and fan speed from anywhere in the room.

#### **Clean Air Ionizer**

With this feature, the electronic air purifier is energized to remove pollen and impurities from the air, improving your comfort.

#### Effortless™ Clean Filter

Our antibacterial filter reduces bacteria, room odors and other airborne particles for a healthier, more comfortable environment.

#### SpaceWise® Adjustable Side Panels

With the Adjustable Side Panels, the side panels will extend to best fit your window.

#### Power Cord

Comes with an extra long three-prong cord — makes extension cords unnecessary.

#### Effortless<sup>™</sup> Restart

Automatically resumes operating at its previous settings when power is restored to your unit.

#### **Clean Filter Alert**

ENERGY STAR®

Alert notifies you when your filter needs to be cleaned so you don't have to keep track of it yourself.

#### Ready-Select<sup>®</sup> Controls

Easily select options with the touch of a button.



Performance	BTUs
Cool	22,000/21,600


# **FRIGID**AIRE

1.1			<u> </u>		<b>_</b> _	<b>L</b>
	lom	1e	CO	m	ГО	rt
	••••					

FFRE2233S2 Heavy-Duty Air Conditioner

Performance	
BTU (Cool)	22,000/21,600
Dehumidification (Pints/Hour)	7.2
Cool Area (Up To Sq. Ft.)	1,300
Energy Efficiency Ratio	10.3
Electrical	
Volts	230/208
Amps (Cool)	9.6/10.5
Watts (Cool)	2,135/2,095
Length of Power Cord (Min./Max.)	5'/6'
Plug Type (NEMA)	LCDI (6-15P)
Features	
Electronic Controls	Ready-Select* Controls
	3/3
Low Voltage Start-Up	Yes
Auto Cool Function	Yes
Energy Saver Mode	Yes
Sleep Mode	Yes
Filter Check	Yes
24-Hour On/Off Timer	Yes
Clean Air Ionizer	Yes
Remote Control	Full-Function Remote T'Stat
Air CFM (High/Med/Low)	523/485/445
Air Direction Control	8-Way
Fresh Air/Exhaust Vent/Closed	Yes/Yes/Yes
Filter Type	Antibacterial Mesh
Filter Access	Tilt-Out
Slide-Out Chassis	Yes
Window Mounting Kit (Included)	Pleated Quick Mount
Warranty <sup>1</sup>	Yes
Certifications	
ENERGY STAR*	Yes
Performance	AHAM
Specifications	
•	R410a

<sup>1</sup>Warranty 5 year sealed system/1 year full parts and labor.



NOTE: For planning purposes only. Always consult local and national electric codes. Refer to Product Installation Guide for detailed installation instructions on the web at frigidaire.com.



Product Dimensions		Wi
A - Height	18-5/8″	D -
B-Width	26-1/2"	Ε-
C-Depth	26-1/2"	Wa

Window Dimensions	
D - Height (Min.)	19-1/2″
E - Width (Min./Max.)	31"/42"
Wall Cutout Dimensions	
F - Max. Wall Thickness	10″
Height	18-7/8″
Width	26-3/4"

Accessories information available on the web at **frigidaire.com** 

#### FRIGIDAIRE.

USA • 10200 David Taylor Drive • Charlotte, NC 28262 • 1-800-FRIGIDAIRE • frigidaire.com CANADA • 5855 Terry Fox Way • Mississauga, ON L5V 3E4 • 1-800-265-8352 • frigidaire.ca