# Thermo Scientific Thermolyne Small Benchtop Muffle Furnaces

#### Fast heatup and outstanding energy efficiency



# Available in two capacities that reach a maximum temperature of 1100°C

- Digital single setpoint temperature control to 1100°C
- Dual display shows actual temperature and setpoint
- Ceramic fiber insulation designed to permit faster heatup, reducing energy consumption
- Embedded heating elements on top and both sides designed to improve temperature uniformity
- Drop-down door doubles as a shelf for loading and unloading

- Door safety switch stops power to heating elements when door is opened
- Thermocouple break protection cuts power to heating elements, preventing failure runaway condition
- 0.95cm (0.38in.) diameter port in chamber rear for monitoring temperatures with independent measuring devices

## **Temperature controller options**

- Control A1
- See page 6 for control details

#### **APPLICATIONS**

- Heat treatment of small steel parts
- Conducting gravimetric analysis
- Determination of volatile and suspended solids

Cat. No.	Capacity	Temp. Range	Temp. Stability (Uniformity)	Interior D x W x H	Exterior L x W x H	Electrical	Shipping Weight	Plug Type
FB1315M	1.3L (0.04 cu. ft.)	100° to 1100°C	±0.3°C at 1000°C (±7.8°C at 1000°C)	13 x 10.3 x 9.8cm (5 x 4 x 3.8in.)	33 x 23 x 36cm (13 x 9 x 14in.)	120V 50/60Hz 1060w;8.9A	9kg (20 lb.)	I I
FB1318M	1.3L (0.04 cu. ft.)	100° to 1100°C	±0.3°C at 1000°C (±7.8°C at 1000°C)	13 x 10.3 x 9.8cm (5 x 4 x 3.8in.)	33 x 23 x 36cm (13 x 9 x 14in.)	208V 50/60Hz 1060w;5.1A	9kg (20 lb.)	•
FB1310M	1.3L (0.04 cu. ft.)	100° to 1100°C	±0.3°C at 1000°C (±7.8°C at 1000°C)	13 x 10.3 x 9.8cm (5 x 4 x 3.8in.)	33 x 23 x 36cm (13 x 9 x 14in.)	240V 50/60Hz 1060w;4.4A	9kg (20 lb.)	-
FB1314M	1.3L (0.04 cu. ft.)	100° to 1100°C	±0.3°C at 1000°C (±7.8°C at 1000°C)	13 x 10.3 x 9.8cm (5 x 4 x 3.8in.)	33 x 23 x 36cm (13 x 9 x 14in.)	100V 50/60Hz 1060w;10.6A	9kg (20 lb.)	Ţ.
FB1310M-33CN	1.3L (0.04 cu. ft.)	100° to 1100°C	±0.3°C at 1000°C (±7.8°C at 1000°C)	13 x 10.3 x 9.8cm (5 x 4 x 3.8in.)	33 x 23 x 36cm (13 x 9 x 14in.)	240V 50/60Hz 1060w;4.4A	9kg (20 lb.)	(1) 10A
FB1310M-33CH	1.3L (0.04 cu. ft.)	100° to 1100°C	±0.3°C at 1000°C (±7.8°C at 1000°C)	13 x 10.3 x 9.8cm (5 x 4 x 3.8in.)	33 x 23 x 36cm (13 x 9 x 14in.)	240V 50/60Hz 1060w;4.4A	9kg (20 lb.)	•••
FB1310M-33UK	1.3L (0.04 cu. ft.)	100° to 1100°C	±0.3°C at 1000°C (±7.8°C at 1000°C)	13 x 10.3 x 9.8cm (5 x 4 x 3.8in.)	33 x 23 x 36cm (13 x 9 x 14in.)	240V 50/60Hz 1060w;4.4A	9kg (20 lb.)	
FB1415M	2.1L (0.07 cu. ft.)	100° to 1100°C	±0.5°C at 1000°C (±5.0°C at 1000°C)	15.2 x 12.7 x 10.8cm (6 x 5 x 4.25in.)	40 x 25 x 37cm (15.8 x 10 x 14.5in.)	120V 50/60Hz 1450w;12.0A	12.7kg (28 lb.)	I.I
FB1418M	2.1L (0.07 cu. ft.)	100° to 1100°C	±0.5°C at 1000°C (±5.0°C at 1000°C)	15.2 x 12.7 x 10.8cm (6 x 5 x 4.25in.)	40 x 25 x 37cm (15.8 x 10 x 14.5in.)	208V 50/60Hz 1520w;7.3A	12.7kg (28 lb.)	•
FB1410M	2.1L (0.07 cu. ft.)	100° to 1100°C	±0.5°C at 1000°C (±5.0°C at 1000°C)	15.2 x 12.7 x 10.8cm (6 x 5 x 4.25in.)	40 x 25 x 37cm (15.8 x 10 x 14.5in.)	240V 50/60Hz 1520w;6.3A	12.7kg (28 lb.)	••
FB1410M-33	2.1L (0.07 cu. ft.)	100° to 1100°C	±0.5°C at 1000°C (±5.0°C at 1000°C)	15.2 x 12.7 x 10.8cm (6 x 5 x 4.25in.)	40 x 25 x 37cm (15.8 x 10 x 14.5in.)	240V 50/60Hz 1520w;6.3A	12.7kg (28 lb.)	•••
FB1410M-33CN	2.1L (0.07 cu. ft.)	100° to 1100°C	±0.5°C at 1000°C (±5.0°C at 1000°C)	15.2 x 12.7 x 10.8cm (6 x 5 x 4.25in.)	40 x 25 x 37cm (15.8 x 10 x 14.5in.)	240V 50/60Hz 1520w;6.3A	12.7kg (28 lb.)	(1) 10A
FB1410M-33-CH	2.1L (0.07 cu. ft.)	100° to 1100°C	±0.5°C at 1000°C (±5.0°C at 1000°C)	15.2 x 12.7 x 10.8cm (6 x 5 x 4.25in.)	40 x 25 x 37cm (15.8 x 10 x 14.5in.)	240V 50/60Hz 1520w;6.3A	12.7kg (28 lb.)	•••
FB1410M-33-UK	2.1L (0.07 cu. ft.)	100° to 1100°C	±0.5°C at 1000°C (±5.0°C at 1000°C)	15.2 x 12.7 x 10.8cm (6 x 5 x 4.25in.)	40 x 25 x 37cm (15.8 x 10 x 14.5in.)	240V 50/60Hz 1520w;6.3A	12.7kg (28 lb.)	
FB1414M	2.1L (0.07 cu. ft.)	100° to 1100°C	±0.5°C at 1000°C (±5.0°C at 1000°C)	15.2 x 12.7 x 10.8cm (6 x 5 x 4.25in.)	40 x 25 x 37cm (15.8 x 10 x 14.5in.)	100V 50/60Hz 1450w;14.5A	12.7kg (28 lb.)	Ţ.

### Hearth Plates

Cat. No.	For Use With			
PH44X1	FB1300 Small Muffle Furnace			
PH48X1	FB1400 Small Muffle Furnace			

**Ordering Information:** Replacement heating elements and thermocouples available separately

Includes: Thermocouple, line cord, and hearth plate to protect bottom of unit

Warranty<sup>¥</sup>: 1 year (parts and labor)

Certifications: -33 units are CE marked, all other units are CSA approved