

8 4700 W. 160th St. Cleveland, OH 44135 PH:800-321-9532 FX:800-321-9535 www.oatey.com

TECHNICAL SPECIFICATION

TUB-N-TILE CAULK



TECHNICAL SPECIFICATION: Oatey Tub-N-Tile Caulk is a flexible, acrylic latex general purpose sealant recommended for caulking bathtubs, sinks, showers and lavatories. Tub-N-Tile Caulk can also be used on most common building products such as concrete, metal, wood, marble, glass and brick. Tub-N-Tile Caulk is mold and mildew resistant.



PHYSICAL/CHEMICAL PROPERTIES

Appearance	White
pН	9.0 ± 1.0
Tack Free Time	1 Hour
Full Cure	36 Hours
Shelf Life	1 year unopened
VOC Content	250 g/L maximum

DIRECTIONS FOR USE

Clean off any dirt or dust particles with water. Do not use soap. Using a utility knife, remove any remnants of old caulking. New caulk will not adhere well to previously cured caulk. Once all caulk residue is removed, clean the area with a mild abrasive or rubbing alcohol. Use a concentrated mildew remover if the area shows signs of mildew. With a 45° angle, cut the tapered nozzle of the caulk tube to the width required to fill the crack or joint. Hold the tube at a 45 angle and use even pressure to apply caulk. Move the tube at an even pace along the joint to be filled. If the bead of caulk is too narrow, re-cut the nozzle to provide a larger opening. Allow the caulk to set for sufficient time. Product should be protected from water for a minimum of 8 hours to allow initial curing. Tub-N-Tile Caulk can be applied at temperatures between 40°F to 90° F. Full clarity of sealant is reached in 3 to 7 days. Sealant may be painted over with latex or oil based paint one hour after sealant is tack-free.

PRECAUTIONS

High vapor concentrations may cause headache, dizziness and nausea. Prolonged or repeated skin contact may lead to drying and irritation. Eye contact may cause irritation.

FIRST AID: If swallowed- Contact physician or poison control center immediately. Eye Contact- Flush eye with copious amounts of water while holding eyelid open. Contact physician if irritation persists. Skin Contact- Wipe material from skin with clean cloth or paper towel. Wash exposed area with soap and water. Contact physician if irritation persists. If inhaled- Seek fresh air. Keep container closed when not in use. DO NOT REUSE EMPTY CONTAINER. KEEP OUT OF REACH OF CHILDREN.

Refer to material safety data sheet for more information. For emergency first aid help, call 1-303-623-5716 COLLECT.

COMMON APPLICATIONS

Oatey Tub-N-Tile Caulk is a flexible, acrylic latex general purpose sealant recommended for caulking bathtubs, sinks, showers and lavatories. Tub-N-Tile Caulk should not be used on copper or brass as discoloration may result. Service Temperature Range for sealant is 0° F to 200° F.

Consult Oatey Technical Department for applications not specifically referenced above.

HAZARDOUS INGREDIENTS (CAS Number)

Mineral Spirits (8052-41-3) Ethylene Glycol (107-21-1) Butyl Benzyl Phthalate (85-68-7)

PRODUCT NUMBER	DESCRIPTION	PACK	CARTON WEIGHT
30240	6 oz. Tub-n-Tile Caulk – Tube	24	14 lbs.
30241	10 oz. Tub-n-Tile Caulk – Cartridge	24	18 lbs.