SPEAKMAN® SE-693

COMBINATION SHOWER & EYEWASH

9 3/4"

(248mm)

7'-0"

TO FLOOR

(2134mm)

69" MAX.

TO FLOOR

(1753 mm)

41"

(1041mm)

ROTATED 90°

24"

(610mm)

1/4" NPTF

5' -5"

1/4"

WASTE

 $(15\bar{2}mm)$

(1651mm)

NPTF

INLET

DESCRIPTION

The SE-693 Safe-T-Zone® features the SE-582 eyewash with dual aerated spray outlets, flip-top dust covers and stainless steel bowl combined on a powder coated galvanized steel stanchion with an impeller action deluge showerhead which is activated by a high visibility yellow pull rod.

SPECIFICATIONS

Showerhead: 8" Cycolac® yellow plastic Flow Control: Internal 20 gpm regulator Valve: 1" NPT female brass, chrome plated. Full flow stay open ball valve.

Activator: Powder coated yellow, aluminum triangular

pull rod

Stanchion: 11/4" IPS galvanized steel piping with

brass fittings

Inlet & Waste: 11/4" NPT female

Finish: DuraJade[™] powder coated finish

Performance: 20 gpm @ 30 psi

EYEWASH: SE-582

Bowl: 300 series stainless steel

Spray Heads: (2) aerated yellow plastic spray

outlets with flip-top dust caps

Valve: 1/2" NPT female brass, chrome plated full flow

stay-open ball valve

Activator: Stainless steel push handle Performance: 3.6 gpm @ 30 psi Compliance: ANSI Z358.1

Universal Emergency Sign Included

OPTIONS

☐ 30GPM	30gpm regulator
\square BH	Brass showerhead
\square FLW	Flow switch
\square FPV	Freeze protection valve
HFO	Hand/Foot operation
\square HS	Hand held spray
\square PSS	Polished stainless steel finish
\square SCV	Self-closing shower valve
\square SPR	Stainless steel pull rod
\square SPV	Scald protection valve
☐ SSBV	Stainless steel ball valves

Stainless steel showerhead

Extended stainless steel pull rod

Top supply

Job Name		
Location		
Architect/Engineer		
Sales Representative		
Wholesaler		
Date	Model #	

Job Name		
Location		
Architect/Engineer		
Sales Representative		
Wholesaler		
Date	Model #	

NOTE: PULL HANDLE SHOWN

42426

 \square SSH

☐ SXPR

 \square TS