



sonic



Sonic™ is a contemporary and affordable stacking chair



Sonic offers exceptional value in a contemporary seating series. A wide range of models suits a variety of interior applications including: meeting rooms, offices, reception areas, cafeterias, waiting rooms and lecture halls. Sonic's versatility is endless.



6508WS shown in Caribbean Surf (CRS).



6513WS shown in Caribbean Surf (CRS).



6509WS shown in in Caribbean Surf (CRS) and Allante, White (A48E).



6514WS shown in in Caribbean Surf (CRS) and Allante, White (A48E).



6524WS shown in in Caribbean Surf (CRS) and Allante, White (A48E).



6515WS shown in in Caribbean Surf (CRS) and Allante, White (A48E).

The series is offered with or without arms, with casters, with sled base, with a mesh back, as a task chair, as a bar height stool, with left or right tablet arms and in a beam seating configuration. Sonic's molded seat and back are strong, durable, easy to clean and available in 10 colors. Frame finishes are standard in Chrome and optional in Black or Tungsten.



6508WS(MB) shown in Caribbean Surf (CRS).



6574 shown in Caribbean Surf (CRS) and Allante, White (A48E).



6509WS(MB) shown in Caribbean Surf (CRS) and Allante, White (A48E).



6514TRWS shown in Caribbean Surf (CRS) and Allante, White (A48E).



6568 shown in Caribbean Surf (CRS) and Allante, White (A48E).



6569 shown in Caribbean Surf (CRS) and Allante, White (A48E).



6559 shown in Caribbean Surf (CRS) and Allante, White (A48E).



Sonic chairs can stack 5 high on floor or 10 high on Sonic's dolly (6517WS).



Sonic Beam - Seat and back options



Polypropylene seat and back



Upholstered seat with polypropylene back



Upholstered seat and back

Sonic beam is an affordable and efficient seating solution to furnish public spaces or reception areas. It's available in multiple lengths to accommodate any seating configuration. Seat and table modules can be placed in any order along the beam. Upholstered seat and back inserts are replaceable for easy maintenance.

Shell colors

Ivory Clouds (IVC)



Tiger Orange (TIO)



Latte Beige (LAB)



Asphalt Night (BLK)



Lip Smacker (LPS)



Caribbean Surf (CRS)



Coffee Bean (CFB)



Sea Glass (SEG)



Platinum (PLT)



Daffodil Day (DFD)



Frame colors



Black (BLK)



Tungsten (TUN)



Chrome (CHM)

Casters and glides



Available on selected models



Optional opaque non marking glides - NC

Tablet



Tablet lifts to 90 degrees for easy access



Wood laminate tablet - available in five finishes

Sonic Models

Description	Dimensions			Seat Height
	W	D	H	
	IN	IN	IN	IN
	mm	mm	mm	mm
 6508WS Armless Stacking Chair with polypropylene seat and back	21.5 546	23 584	33 838	18 457
 6509WS Armless Stacking Chair with upholstered seat and polypropylene back	21.5 546	23 584	33 838	18.5 470
 6511WS Armless Stacking Chair with upholstered seat and back	21.5 546	23 584	34 864	18.5 470
 6513WS Stacking Armchair with polypropylene seat and back	23 584	23 584	33 838	18 457
 6514WS Stacking Armchair with upholstered seat and polypropylene back	23 584	23 584	33 838	18.5 470
 6515WS Stacking Armchair with upholstered seat and back	23 584	23 584	34 864	18.5 470
 6518WS Armless Stacking Chair with sled base, polypropylene seat and back	22 559	22.5 572	32.5 826	17 432
 6519WS Armless Stacking Chair with sled base, upholstered seat and polypropylene back	22 559	22.5 572	32.5 826	17.5 445

Description	Dimensions			Seat Height
	W	D	H	
	IN	IN	IN	IN
	mm	mm	mm	mm
 6521WS Armless Stacking Chair with sled base, upholstered seat and back	22 559	22.5 572	33 838	17.5 445
 6523WS Stacking Armchair with sled base, polypropylene seat and back	23 584	22.5 572	32.5 826	17 432
 6524WS Stacking Armchair with sled base, upholstered seat and polypropylene back	23 584	22.5 572	32.5 826	17.5 445
 6525WS Stacking Armchair with sled base, upholstered seat and back	23 584	22.5 572	33 838	17.5 445
 6558 Armless Bar Height Stool with polypropylene seat and back	22 559	23 584	42 1067	28 711
 6559 Armless Bar Height Stool with upholstered seat and polypropylene back	22 559	23 584	42 1067	28.5 724
 6561 Armless Bar Height Stool with upholstered seat and back	22 559	23 584	42.5 1080	28.5 724
 6563 Bar Height Stool with arms, polypropylene seat and back	23 584	23 584	42 1067	28 711

Sonic Models

Description	Dimensions			Seat Height
	W	D	H	
	IN	IN	IN	IN
	mm	mm	mm	mm
 <p>6564 Bar Height Stool with arms, upholstered seat with polypropylene back</p>	23 584	23 584	42.5 1080	28.5 724
 <p>6565 Bar Height Stool with arms, upholstered seat and back</p>	23 584	23 584	42.5 1080	28.5 724
 <p>6573 Armchair with casters, polypropylene seat and back</p>	23 584	21 533	32 813	17.5 445
 <p>6574 Armchair with casters, upholstered seat and polypropylene back</p>	23 584	21.5 546	32 813	18 457
 <p>6575 Armchair with casters, upholstered seat and back</p>	23 584	21.5 546	32.5 826	18 457
 <p>6577 Armless chair with casters, polypropylene seat and back</p>	21 533	21 533	33 838	17.5 445
 <p>6578 Armless chair with casters, upholstered seat and polypropylene back</p>	21 533	21.5 546	33 838	18 457
 <p>6579 Armless chair with casters, upholstered seat and back</p>	21 533	21.5 546	32.5 826	18 457

Description	Dimensions			Seat Height
	W	D	H	
	IN	IN	IN	IN
	mm	mm	mm	mm
 <p>6508TRWS Armless chair with right tablet arm polypropylene seat and back</p>	24.75 629	26.5 673	32.5 826	18 457
 <p>6509TRWS Armless chair with right tablet arm upholstered seat and polypropylene back</p>	24.75 629	26.5 673	32.5 826	18.5 470
 <p>6511TRWS Armless chair with right tablet arm upholstered seat and back</p>	24.75 629	26.5 673	32.5 826	18.5 470
 <p>6513TRWS Armchair with right tablet arm polypropylene seat and back</p>	25 635	26.5 673	32.5 826	18 457
 <p>6514TRWS Armchair with right tablet arm upholstered seat and polypropylene back</p>	25 635	26.5 673	32.5 826	18.5 470
 <p>6515TRWS Armchair with right tablet arm upholstered seat and back</p>	25 635	26.5 673	32.5 826	18.5 470
 <p>6567 Task chair with arms, polypropylene seat and back</p>	23 584	20.5 521	32.5 826	15.5-20.5 394-521
 <p>6568 Task chair with arms, upholstered seat and polypropylene back</p>	23 584	20.5 521	32.5 826	16-21 406-533

Sonic Models

Description	Dimensions			Seat Height
	W	D	H	
	IN	IN	IN	IN
	mm	mm	mm	mm
 6569 Task chair with arms, upholstered seat and back	23 584	20.5 521	33 838	16-21 406-533
 6517WS Stacking Chair Dolly, chairs stack up to 10 high on dolly. Black only	23.25 591	24.75 629	12.25 311	N/A N/A

Description	Dimensions			Seat Height
	W	D	H	
	IN	IN	IN	IN
	mm	mm	mm	mm
 6526 Ganging Clamp set, only for use with sled base models	0.75 19	5.75 146	1.25 32	N/A N/A
 6522 Ganging Clamp set, only for use with 4 legged models	0.87 22	7.75 197	1.5 38	N/A N/A

For a complete listing of SONIC models, please refer to the Global Price List.



Cover: 6508WS Polypropylene seat and back shown in Daffodil Day (DFD) and Tungsten (TUN) finish.



Global - Canada, The Global Group
 1350 Flint Rd., Downsview ON Canada M3J 2J7
 Sales & Marketing: Tel (1-877) 446-2251
 Customer Service: Fax (800) 361-3182
 Government Customer Service: Fax (416) 739-6319

Global - U.S.A.
 17 West Stow Road P.O. Box 562
 Marlton New Jersey U.S.A. 08053
 Tel (856) 596-3390 (800) 220-1900
 Fax (856) 596-5684

Global - International
 560 Supertest Road Downsview
 Ontario Canada M3J 2M6
 Tel (416) 661-3660 (800) 668-5870
 Fax (416) 667-1821

GGI Office Furniture (UK) Ltd.
 Global Way Darwen
 Lancashire UK BB3 ORW
 Tel +44(0) 1254 778500
 Fax +44(0) 1254 778519

Visit us on the World Wide Web at www.globaltotaloffice.com Offices throughout Canada, United States, United Kingdom, France, Australia and Brazil. Distribution around the world. A member of the Global Group. © 2014 ©™ Trade-Marks of GLOBAL TOTAL OFFICE. These products may be covered by one or more issued patents or pending patent applications in Canada, the U.S. and elsewhere. All intellectual property rights in applicable trademarks, patents and industrial designs are strictly reserved. Made in Canada. Specifications are correct at time of printing. Printed in Canada. Creative / Global Group Design Center 151214 14.0212