Small Department Shredder 40506 Dahle Professional Shredder





Known for its power and waste capacity the Dahle Small Department Professional Shredder is designed to accommodate the needs of most small departments. This stripcut machine offers a 1/4" particle size and is able to shred to security level 2 standards. It's a perfect shredder for destroying marketing plans, health records, and any other confidential information that should not be seen by others.

Dahle's 40506 is built with a 12" feed opening and can shred up to 32/36 sheets of paper at a time. This machine can accommodate both letter and legal size paper with ease. All you need to do is decide what document to shred and the shredder will take care of the rest.

Energy conservation continues to be a top priority at Dahle. Each shredder comes equipped with the revolutionary SmartPower Energy Management System. This multistage system reduces power consumption after ten minutes of sitting idle (sleep mode), and completely powers down after an additional 20 minutes of inactivity. Dahle SmartPower will appeal to those interested in conserving energy as well as reducing electrical costs.

In order to provide slip free power to the cutting cylinders, a steel chain and gears connect the two components and provide maximum shredding capacity. Removing staples and paper clips are a thing of the past. Dahle shredders can easily accommodate these items without harming the machine and saving you time in the process.

Dahle's shredders are German Engineered using the latest technology and finest materials. The end result is a quality machine and peace of mind in knowing your Dahle shredder will provide many years of trouble free operation.













Features

• Feed Opening: 12"

• Sheet Capacity: 32/36

• Shred Size: 1/4"

• Security Level: P-2

• SmartPower Management

German Engineered



Dahle Professional shredder with built in user-friendly opening for CD/ DVD destruction.



all of the shredder's functions such as cutting cylinders, a steel chain & gears



The easy-to-use command dial controls In order to provide slip free power to the power up, reverse, and continuous run. connect the two for maximum capacity.

Sp	Specifications															
Model	Feed Width	Capacity #20 / #16	Security Level	Shred Size	Waste Volume	Speed	Decibel Level	Staples/Clips	CDs/DVDs		ures/Capabi CleanTEC®		ESP	Auto Oiler	Dimensions	Weight
40506	12"	32 / 36	P-2	1/4"	38 gal	16 f/m	46 dB	•	•	•					34 ½" x 29" x 20"	132 lbs

All performance data has been established using #20 / #16 bond 8 1/2" x 11" paper. Different paper qualities may yield different results.



(800) 995.1379 / www.dahle.com



Authorized Dealer