## Large Format Trimmers 472 Premium Rolling Trimmer





Dahle's 472 Premium Rolling Trimmer offers six feet of superior cutting performance. It features all the benefits you'd expect from our Premium Series, with an extra-long 72" cutting length. Now available with an optional stand (472 S) for optimal trimming height and comfort.

The Dahle 472 is a German Engineered commercial grade tool, with the ability to cleanly cut oversize banners, mat board, and fine art paper with the highest level of accuracy. It features a ground rotary blade,

and a self-sharpening cutting system that cuts and sharpens in either direction. This action maintains the blade's precision graduated edge, allowing it to remove even the tiniest sliver of paper, and produce a clean, burr free cut – each and every time.

As with all Dahle products, safety is at the forefront of design, and this trimmer is no exception. To keep hands in the safe zone, the trimmer's blade is almost entirely enclosed- which virtually eliminates the chance of injury. Holding your work securely is no longer necessary. The integrated, automatic clamping system provides even pressure, and prevents your work from shifting. For measuring, this base contains carefully screened guides, and an adjustable backstop – which is the easiest way to ensure consistent accuracy during repetitive cutting.



## **Features**

- Self sharpening blade cuts in both directions
- Blade is encased in protective housing for safety
- Cuts paper, canvas, and mat board
- Automatic paper clamp holds work securely
- Thick walled aluminum guide bar for durability
- Sturdy metal base with preprinted guides
- Imprinted protractor for angled cuts
- German Engineered for precision and accuracy
- Optional Stand for optimal trimming height

## 

Dahle North America, Inc. 49 Vose Farm Road Peterborough, NH 03458 (800) 995.1379 / www.dahle.com





*The precision ground, circular blade cuts and sharpens in both directions.* 

The automatic clamp securely holds your work in place and prevents shifting.

Specifications					
ltem	Cut Length	Capacity	Dimensions	Optional Stand	
472	72"	12 Sheets	79 ½" x 15 ½"	# 799	

$\bigcap$	Authorized Dealer	