MOBILE WORK PLATFORMS

Platforms provide a secure movable work space at a variety of heights above floor level. 800 lbs capacity. Rigid 1" square tubing. 4" rear casters provide mobility and rubber tipped legs add traction while in use. Steps are 7" deep. Perforated or Grip Strut Tread for slip-resistant footing. Meets OSHA standards.

ALUMINUM WORK PLATFORMS

Lightweight platform provides a stable and solid work surface that is both weather and corrosion resistant. 300 lbs capacity. Rigid 1" square tubing. 4" rear tilt-back casters provide in the stable stable



4" rear tilt-back casters provide mobility and rubber tipped legs add traction while in use. Solid ribbed extruded step or Grip Strut Tread for slip-resistant footing. Meets OSHA standards.





EGA PRODUCTS MANUFACTURERS OF MATERIAL HANDLING AND STORAGE EQUIPMENT

Aluminum Models

Model	B2131362	B1893212	B2131641	B1893213	B1893215	B2131518	B1893217
# of Steps	3	3	4	5	2	3	2
Tread Type	Perforated	Grip-Strut	Grip-Strut	Perforated	Ribbed	Ribbed	Ribbed
Platform Height	30"	30"	40"	50"	20"	30"	20"
Platform Width	30"	24"	24"	30"	24"	24"	24"
Platform Depth	35"	35"	49"	35"	35"	42"	35"
O/A Height	30"	30"	40"	82"	20"	30"	52"
0/A Width	32"	27"	27"	32"	27"	27"	27"
0/A Length	50"	49"	69"	61"	47"	60"	47"
Assembled	Assembled	Assembled	Assembled	Assembled	Assembled	Assembled	Assembled
Brand	EGA Products						
Capacity	800lbs	800lbs	800lbs	800lbs	300lbs	300lbs	300lbs
Color Finish	Gray	Gray	Gray	Gray	Mill	Mill	Mill
Construction	Steel	Steel	Steel	Steel	Aluminum	Aluminum	Aluminum
Incline Angle	50	60	60	60	60	60	60
Hand Rails	N	N	N	Υ	N	N	Υ