TRUCK/DOCK

LADDER

Truck/Dock Ladders with 50-Degree Safety Angle are designed to promote safety and productivity. 50-degree ladder angle enables user to turn and descend facing forward while carrying bulky load. The large platform and each step feature serrated tread for slipresistant footing. Removable back and side chain enable front or side loading from trailer. Large rear wheels roll smoothly over rough terrain. Meets OSHA Standards.





| Model | B1893200 | B1893201 | B1893202 | B1893199 | B1893206 | B1893203 |
|-----------------|--------------|--------------|--------------|--------------|--------------|--------------|
| # of Steps | 4 | 4 | 5 | 5 | 6 | 6 |
| Platform Height | 40" | 40" | 50" | 50" | 60" | 60" |
| Platform Width | 36" | 36" | 36" | 36" | 36" | 36" |
| Platform Depth | 48" | 48" | 48" | 48" | 48" | 48" |
| O/A Height | 70" | 70" | 80" | 80" | 90" | 90" |
| 0/A Width | 46" | 46" | 46" | 46" | 46" | 46" |
| 0/A Length | 77" | 77" | 86" | 86" | 94" | 94" |
| Assembled | Unassembled | Assembled | Assembled | Unassembled | Unassembled | Assembled |
| Brand | EGA Products |
| Capacity | 800 lbs. |
| Color Finish | Blue | Blue | Blue | Blue | Blue | Blue |
| Construction | Steel | Steel | Steel | Steel | Steel | Steel |
| Incline Angle | 50° | 50° | 50° | 50° | 50° | 50° |