

Global Industrial™ Non-Touch Digital Thermometer



Model #695746



Features:

- Measure body temperature with high accuracy
- Switchable for °C or °F
- Buzzer function
- LCD display with backlight
- Automatic range selection; resolution is 0.1°C (0.1°F)
- The latest 20 measurement data can be memorized and stored

Specifications

- Measured temperature range: 33.0°C ~ 43.0°C
- Proper measuring distance range: 3 to 5 cm (1.18 to 1.97 inches)
- Automatic shut-down: 13s
- Accuracy:
 - 33 ~ 43°C (91.4~109.4°F): ±0.2°C (32.4°F)
 - < 33°C (91.4°F): ±2.0°C (35.6°F)
 - > 43°C (109.4°F): ±2.0°C(35.6°F)
- Display resolution: 0.1°C (0.1°F)
- Power supply: 2 AAA batteries (Not Included)
- Operating mode: Non-stop with awoken button
- Net weight: 0.11kg
- Dimensions: 154 x 87.7 x 44mm
- Anti-shock type: Internal power supply equipment
- Storage temperature: -20°C~55°C (-4°F~13.1°F)
- Operation ambient temperature: 16°C~35°C (60.8°F~95.0°F). The best temperature is 25°C
- Relative humidity: ≤85%RH
- Protection against electric shock: BF type application part
- Maximum permissible error:
 - ±0.2°C within the range of 33°C to 43°C
 - ±0.2°C outside the range of 33°C to 43°C
- Clinical accuracy:
 - 1) Clinical deviation: ≤ ± 0.3°C
 - 2) Clinical standard deviation: ≤ ± 0.3°C
- Clinical repeatability: ≤± 0.3°C
- Memory data: 20 records
- High fever warning: 5 beeps
- Certification: CE & FCC, FDA