



Z1395 YARD HYDRANT Exposed Head, Non-Freeze

SPECIFI	CATION SHEET
TAG	

Dimensional Data (inches and [mm]) are Subject to Manufacturing Tolerances and Change Without Notice





Depth of Bury Feet	B+ Dim. Feet	Approx. Wt. Lbs. [kg]
2 [610]	4 1/2 [1372]	15 [7]
3 [914]	5 1/2 [1676]	19 [9]
4 [1219]	6 1/2 [1981]	23 [10]
5 [1524]	7 1/2 [2286]	27 [12]
6 [1829]	8 1/2 [2591]	31 [14]
8 [2438]	10 1/2 [3200]	39 [18]

ENGINEERING SPECIFICATION: ZURN Z1395 Exposed, non-freeze yard hydrant, with Dura-Coated cast iron head and lift handle with lock option. Bronze interior parts and galvanized steel casing with bronze valve housing and 1/8 [3] IP drain port in housing.

Note: 'B' dim. based on outlet connection 30 [762] above ground.

OPTIONS (Check/specify appropriate options)	<u>ltem</u>	PARTS LIST Name	Quan.
SUFFIXES AC	7 8 10 13	Operating Coupling Packing Operating Rod Plunger	1 1 1

REV. E DATE: 8/29/03 C.N. NO. 91237

DWG. NO. 58884 PRODUCT NO. Z1395

*WHEN ORDERING REPLACEMENT PARTS SPECIFY Y DIM.

^{**} Non-Freeze feature will not function when (-VB suffix) vacuum breaker is specified.