

JWBS-15, 15" BANDSAW, 1-3/4HP, 115/230V

714600

Designed to perform, the JET 15" bandsaw delivers more re-saw capacity, greater throat depth and the horsepower you need to tackle bigger boards, create smoother edges and master the intricate cuts. The heavy-duty cast-iron fence system is built to give you the sturdiness and support you need for every project and features a micro-adjust dial for exact placement. The table is slotted and the guide post has a stress-free magnetic door on the front for efficient blade changes. Large, independently adjustable guides are tool-less to save you time on set up. The JET 15" steel frame bandsaw is engineered to build great projects through superior performance.



FEATURES

- 14" Resaw capacity for cutting large pieces of wood, slicing veneers and cutting book matched panels
- 21-1/2" x 16" precision ground cast iron table for added stability and work support
- Fence system features a micro-adjustable, dual-position side plate
- Tool-less, independently adjustable, upper and lower ball bearing guides
- Rigid, four-sided guide post with rack and pinion adjustment for optimum blade support
- Easy-to-read blade tension scale can be viewed through upper door window
- Single knob adjustment simplifies the blade tracking process
- Blade tracking window provides clear view of blade during tracking
- Heavy duty tensioning with quick release features three settings: full tension, partial tension and full release
- Cast iron trunnion for maximum support and stability
- Slotted table allows for front blade removal
- Cast iron handwheels and ergonomically designed knobs make adjustments smooth and easy
- Round table insert features leveling screws for precise adjustment
- Conveniently located dual 4" dust collection ports catch dust and chips at the source
- Table tilts 5° left and 45° right to accommodate a wide variety of cuts



JET RED ASSURANCE 5-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

JWBS-15, 15" BANDSAW, 1-3/4HP, 115/230V

714600

SPECIFICATIONS

Band Saw Size/Wheel Diameter (In.)	14-3/4
Cutting Capacity Width (In.)	14-1/8
Cutting Capacity Height (In.)	14
Blade Length (In.)	133
Blade Speed (SFPM)	3100
Table Size (L x W) (In.)	21-1/2 x 16 x 2
Blade Width (In.)	1/2", 6TPI
Maximum Saw Blade Width (In.)	1
Minimum Saw Blade Width (In.)	1/8
Table Tilt (Deg.)	-5,45
Table Height from Floor (In.)	35
Dust Collection Minimum CFM Required (CFM)	400
Dust Port Outside Diameter (In.)	4 (x2)
Motor Power (HP)	1-3/4
Motor Phase (PH)	1
Motor Voltage (V)	115/230
Prewired Voltage (V)	115



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE