

DOOR LOUVERS MODEL ADL/SDL


Description

Heavy Duty Extruded Aluminum or Steel construction designed to allow the transfer of air through a door while also maintaining privacy. Ideal for use with 1-3/8" to 2-1/4" thick wood or metal doors.

Installation

- 1. Measure inside dimensions of unit to ensure proper fit.
- Cut hole in door in accordance with door manufacturer's recommendation.
- 3. Place the door louver (Figure 1) into the opening.
- 4. Insert and start all screws before tightening.
- Tighten all screws using a crisscross pattern. Use caution to avoid stripping or over tightening screws.
- 6. Place the Slip Fit Collar (Figure 2) on the opposite side of door. Push into place and secure it using the same procedure as above.

| Aluminum Model | Steel Model | Hole Opening | | Actual OD | |
|-------------------|----------------|--------------|--------|-----------|---------|
| No. | No. | W | jЙ | W | H |
| ADL-8x8 | SDL-8x8 | 8 1/2" | 8 1/2" | 10 1/4" | 10 1/8" |
| ADL-10x4 | SDL-10x4 | 10 1/2 | 4 1/2 | 12 1/4 | 6 1/8 |
| ADL-12x8 | SDL-12x8 | 12 1/2 | 8 1/2 | 14 1/4 | 10 1/8 |
| ADL-12x12 | SDL-12x12 | 12 1/2 | 12 1/2 | 14 1/4 | 14 1/8 |
| ADL-14x8 | SDL-14x8 | 14 1/2 | 8 1/2 | 16 1/4 | 10 1/8 |
| ADL-14x12 | SDL-14x12 | 14 1/2 | 12 1/2 | 16 1/4 | 14 1/8 |
| ADL-16x8 | SDL-16x8 | 16 1/2 | 8 1/2 | 18 1/4 | 10 1/8 |
| ADL-16x16 | SDL-16x16 | 16 1/2 | 16 1/2 | 18 1/4 | 18 1/8 |
| ADL-18x12 | SDL-18x12 | 18 1/2 | 12 1/2 | 20 1/4 | 14 1/8 |
| ADL-20x10 | SDL-20x10 | 20 1/2 | 10 1/2 | 22 1/4 | 12 1/8 |
| ADL-20x12 | SDL-20x12 | 20 1/2 | 12 1/2 | 22 1/4 | 14 1/8 |
| ADL-20x14 | SDL-20x14 | 20 1/2 | 14 1/2 | 22 1/4 | 16 1/8 |
| ADL-20x16 | SDL-20x16 | 20 1/2 | 16 1/2 | 22 1/4 | 18 1/8 |
| ADL-20x20 | SDL-20x20 | 20 1/2 | 20 1/2 | 22 1/4 | 22 1/8 |
| ADL-24x12 | SDL-24x12 | 24 1/2 | 12 1/2 | 26 1/4 | 14 1/8 |
| ADL-24x16 | SDL-24x16 | 24 1/2 | 16 1/2 | 26 1/4 | 18 1/8 |
| ADL-24x18 | SDL-24x18 | 24 1/2 | 18 1/2 | 26 1/4 | 20 1/8 |
| ADL-24x24 | SDL-24x24 | 24 1/2 | 24 1/2 | 26 1/4 | 26 1/8 |






Figure 2 - Slip Fit Collar

LIMITED WARRANTY

All products manufactured are warranted by Air Conditioning Products Company (ACP) to be free from original defects in workmanship for a period of one year from date of shipment, under conditions of normal use and service. ACP will replace or repair any defective parts upon return to our plant, freight prepaid. This limited warranty will, in no way, include the payment of labor charges for field replacement of defective parts, installation, repairs of adjustments, or any other work done. Back charges will not be accepted for any reason unless ACP has given prior written permission, nor will ACP be responsible for consequential damages of any character, no limited warranty expressed or implied will supersede the foregoing.