

# **MODEL 104-A**

## **THREE ROLL FILM CAPACITY FLOOR MODEL WRAPPER**



### **Features of the 104-A Wrapper**

- Standard 115 Volt Power Supply
- Solid State Controlled Film Cut Off Rod
- 8" by 15" Thermostatically Controlled Hot Plate With Non-Stick, Replaceable Teflon Cover
- Heavy Gauge Welded Aluminum Frame
- Aluminum And Stainless Steel Construction
- Stainless Steel Wrapping Surface
- Adjustable Foot Pads For Easy Leveling On Uneven Floors
- Stretch Film - 20" Maximum Width
- Easy To Use Film Selector Feature
- Adjustable Film Tension
- Available In Extended Widths - 24", 30" And 36"

### **Specifications and Options**

**Power Requirement:** 115 Volt, 6.5 Amps, 60 Cycles

**Wattage:** 725 Watts

**Working Height:** 36" (91 cm)

**Overall Dimensions:** 26" D, 25" W, 38" H  
(66 D, 64 W, 97 H cm)

**Weight:** 65 lbs. (30 kg)

#### **Options:**

- 12 Hour Timer
- All Stainless Steel Construction (S104A)
- Removable Power Pack (104R)
- 220 Volt Power Supply
- Stainless Steel Wings (W24ST), 24" W, 14" D
- Accessory Storage Rack (ASR), 22" W, 14" D, 12" H
- Label Dispensers (Various Sizes Available)