

# 600A



## Features of the 600-A

- Standard 115 Volt Power Supply
- Solid State Controlled Film Cut Off Rod
- 6" by 15" Thermostatically Controlled Hot Plate With Non-Stick, Replaceable Teflon Cover
- Heavy Gauge Aluminum Base
- Aluminum And Stainless Steel Construction
- Stainless Steel Wrapping Surface
- Large Rubber Feet
- Stretch Film - 20" Maximum Width
- Available in 2 Roll (800-A) and 3 Roll (850-A)

## Specifications and Options

Power Requirement: **115 Volt, 6.5 Amps, 60 Cycles**

Wattage: **725 Watts**

Working Height: **Table Top Units**

Overall Dimensions: **26" D, 22 1/2" W, 5" H**  
(66 D, 57 W, 13 H cm)

Weight: **30 lbs. (14 kg)**

- Options:
- 12 Hour Timer
  - 8" by 15" Hot Plate with Belly Guard
  - 220 Volt Power Supply
  - Model 50 Stand