

NIGHTHAWK

NIGHTHAWK BLUETOOTH LAPEL MICROPHONE FOR TWO-WAY RADIO



The **Nighthawk Bluetooth Lapel Microphone** is the ultimate body-worn microphone designed specifically for law enforcement. The "Connect & Go" earpiece option allows you to customize the unit to fit your job detail. Features like durable housing, a strategically placed pairing light, full-shift talk-time & no wires makes this unit the ideal choice for the law enforcement industry.



FEATURES & BENEFITS:

- ▶ Body-worn microphone with acoustic airtube removeable earpiece for improved comfort and safety.
- ▶ All day App operations on a single charge.
Talk time 12 hrs. / Standby: 150 hrs.
- ▶ MFB for answer/hang up, power on/off and pairing functions.
- ▶ Designed with a 3.5mm audio jack to accommodate an external earpiece or an external microphone, for even more field versatility.
- ▶ 500 milliamp rechargeable/replaceable lithium ion battery.
- ▶ Heavy duty housing with rotating body clip and large Push-to-Talk (PTT) button.
- ▶ Includes the soft silicone Fin Ultra eartip, our most comfortable ear tip to date.
- ▶ New updated firmware supports radios with built-in Bluetooth and Smartphone POC (Push-to-Talk Over Cellular) Apps.



KIT INCLUDES:

- REMOVEABLE EARPIECE
- NIGHTHAWK MICROPHONE
- BLUETOOTH RADIO ADAPTER
- A/C WALL CHARGER
- USB CHARGING CABLE

BLUETOOTH VERSION: BLUETOOTH 3.0

BLUETOOTH PROFILES: HSP, HFP, A2DP, AVRCP

BLUETOOTH RF SPEC: CLASS 2

SECURE 128-BIT KEY ENCRYPTION

500MA RECHARGEABLE / REPLACEABLE BATTERY

RF POWER: 6dB RF SENSITIVITY: -90dB

RF FREQUENCY: 2.4-2.4835 GHz

AUDIO INPUT 3dB BANDWIDTH: 20kHz

AUDIO INPUT SNR @ 8 kHz: 79dB

AUDIO OUTPUT BANDWIDTH: 20 Hz - 20kHz

CMRR: 50dB

AVERAGE STANDBY CURRENT: 6mA

OPERATION RANGE: 10 METERS

DIMENSIONS: W .75" x H 2.25" x D .75"

WEIGHT: 1.4 OZ.