



AR49 Refrigerator

AF49 Freezer

- Tested to NSF Standard 7 requirements for open food storage.
- Arctic Air products must pass numerous quality control inspections throughout the manufacturing process. All products are operated and monitored for a minimum of thirteen hours prior to packaging and shipping.
- All Arctic Air products come with full one year parts and labor warranties and a five year compressor warranty.

Two Door Reach-in Refrigerators and Freezers



Two Door Reach-in Refrigerators and Freezers

Stainless design. Stellar performance. Superior value.

- Exterior cabinet construction consists of full stainless steel front and sides.
- Electronic thermostat with external digital LED display for accurate control and easy reading.
- Interior cabinet is bright white aluminum liner with full stainless steel floor with coved corners.
- Six adjustable, heavy-duty epoxy coated wire shelves.
- Self contained capillary tube system using environmentally friendly CFC free refrigerant (R404A in freezers and R134A in refrigerators).
- Condensate heating element built into condensate pan for efficient evaporation of excess water.
- Bottom mounted compressor for more efficient operation in coolest area of the kitchen.
- Front accessible, bottom mounted condensing unit is mounted on slide out rack for easy maintenance.

- Self closing doors that remain open at 90 degrees.
 - Magnetic door gaskets are removable and replaceable without tools.
 - Freezer doors have integral factory installed heating element to eliminate condensation.
 - Lockable doors with foamedin-place recessed handles.
 - Larger fan motors and blades for more efficient air flow ensuring faster recovery times.
 - Easy to mount casters (two lockable) are standard with all units.
 - Tested to NSF Standard 7 requirements for open food storage.
 - All Arctic Air products come with full one year parts and labor warranties and a five year compressor warranty.



Model Number	External Dimensions Width Depth* Height**			Doors	Shelves	Cubic Feet	Temperature Range	Cord Length	HP	Amps	NEMA Plug	Crated Weight (lbs.)
AR49	54"	32.75"	82.75"	2	6	49	33°F to 41°F	9	1/2	7	5-15P	455
AF49	54"	32.75"	82.75"	2	6	49	-10°F to +10°F	9	1	12	5-15P	485
*Dooth wi	th door o	non 00°	ΛD40/ΛΕ40 — 57.75"		5" ** 山 /	** Height includes 6" for costors						

*Depth with door open 90° — AR49/AF49 = 57.75'' **Height includes 6'' for casters

Optional Shelf Kit (#65056K)

Each kit contains one shelf and four mounting clips.







