



CT661BISSHV



33.25" x 23.63" x 23" (H x W x D)

Built-in undercounter refrigerator-freezer for residential use, cycle defrost w/deluxe interior, stainless steel wrapped door, thin handle, and white cabinet

Highlights:

Flexible design allows built-in or freestanding use in 24" spaces

Deluxe interior with glass shelves, door storage, and a scalloped wine shelf

Stainless steel wrapped door with professional handle brings luxury to any setting

Improved temperature performance with our unique dual evaporator cooling

Product Features:

Slim undercounter dimensions	Ideal 24" footprint offers full 5.1 cu.ft. storage capacity in a slim fit
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinetry
Stainless steel wrapped door	Durable design with lasting elegance
Professional stainless steel handle	Thin (14mm diameter) stainless steel handle mounted vertically for a sleek look that matches many popular styles of cabinetry
Cycle defrost	This system utilizes user-friendly automatic defrost operation in the fresh food section and efficient manual defrost operation in the freezer compartment
Dual evaporator cooling	Our unique and efficient design separately cools the refrigerator while maintaining zero degrees in the freezer with two evaporators
Zero degree freezer	Frozen food and ice cream stay safe and freezer burn-free in the low temperature freezer compartment
Adjustable glass shelves	Rearrange the refrigerator space to fit any sized item or remove shelves for simple cleanup
Door shelves	Store tall bottles and condiments right on the door for convenient access



CT661BISSHV Specifications:

Overview	
Height	33.25"
Width	23.63"
Depth	23.0"
Depth with door at 90°	45.38"
Capacity	5.1 cu.ft.
Defrost Type	Cycle
Door	Stainless Steel
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Energy Usage/Year	365.0kWh/year
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Weight	100.0 lbs.
Shipping Weight	120.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Factory Reversible
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Refrigerator - Interior Height	18.0"
Refrigerator - Interior Width	21.0"
Refrigerator - Interior Depth	18.0"
Refrigerator - Capacity	4.5 cu.ft
Refrigerator - Shelf Type	Glass
Refrigerator - Shelf Qty	2
Refrigerator - Full Door Shelves	3
Freezer - Interior Height	5.25"
Freezer - Interior Width	19.0"
Freezer - Interior Depth	11.5"
Freezer - Capacity	0.6 cu.ft

Adjustable Shelves	Yes
Wine Bottle Shelving	Yes
Interior Light	Yes
Thermostat Type	Dial
Fan Type	Exterior
Freon	R134a
Freon Amount	2.33
High Side PSI	285.0
Low Side PSI	70.0
Level Legs	4
Compressor Step Height	5.5"
Compressor Step Width	21.0"
Compressor Step Depth	6.0"



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799 info@summitappliance.com www.summitappliance.com