



CT663BCSSADA



32" x 23.75" x 23.5" (H x W x D)

ADA compliant built-in undercounter refrigerator-freezer for residential use, cycle defrost w/deluxe interior, stainless steel exterior, and towel bar handle

Highlights:

32" height fits under lower ADA compliant counters

Flexible design allows built-in or freestanding use in 24" wide spaces

Complete construction in durable stainless steel, with our signature towel bar handle included

Deluxe interior with glass shelves, door storage, and a scalloped wine shelf

Product Features:

ADA compliant	32" high to fit under lower ADA compliant counters
Built-in capable	Make the best use of space by installing your appliance under the counter
Slim undercounter dimensions	Less than 24" wide with a generous storage capacity
Complete stainless steel exterior	Fully wrapped in 304 grade stainless steel
Professional towel bar handle	Curved handle in brushed stainless steel offers a sturdy grip with professional elegance
Cycle defrost	This system utilizes user-friendly automatic defrost operation in the fresh food section and efficient manual defrost operation in the freezer compartment
Zero degree freezer	Frozen food and ice cream stay safe and freezer burn-free in the low temperature freezer compartment
Dual evaporator	Our unique and efficient design separately cools the refrigerator while maintaining zero degrees in the freezer with two evaporators
Adjustable glass shelves	Rearrange refrigerator space to accommodate all sizes or remove shelves for simple cleanup



CT663BCSSADA Specifications:

Overview	
Height	32.0"
Height to Hinge Cap	32.25"
Width	23.75"
Depth	23.5"
Depth with Handle	25.25"
Depth with door at 90°	45.38"
Capacity	5.1 cu.ft.
Defrost Type	Cycle
Door	Stainless Steel
Cabinet	Stainless Steel
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Energy Usage/Year	365.0kWh/year
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Weight	120.0 lbs.
Shipping Weight	148.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Factory Reversible
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Refrigerator - Interior Height	18.0"
Refrigerator - Interior Width	21.0"
Refrigerator - Interior Depth	18.0"
Refrigerator - Capacity	4.5 cu.ft
Refrigerator - Shelf Type	Glass
Refrigerator - Shelf Qty	2
Refrigerator - Full Door Shelves	3
Freezer - Interior Height	5.25"
Freezer - Interior Width	19.0"

Freezer - Interior Depth	11.5"
Freezer - Capacity	0.6 cu.ft
Adjustable Shelves	Yes
Wine Bottle Shelving	Yes
Interior Light	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	2.33 oz.
High Side PSI	285.0
Low Side PSI	70.0
Level Legs	4
Compressor Step Height	5.5"
Compressor Step Width	21.0"
Compressor Step Depth	6.0"



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799 info@summitappliance.com  www.summitappliance.com