

CT66J



33.25" x 23.63" x 23.5" (H x W x D)

Freestanding refrigerator-freezer for general purpose use, with dual evaporator cooling, cycle defrost, and white exterior

Highlights:

Improved temperature performance with our unique dual evaporator cooling

Over 5 cu.ft. of storage capacity in a perfectly sized 24" footprint

Door racks provide convenient storage options

Zero degree freezer compartment

Product Features:

Slim counter height dimensions	Popular 24" footprint offers generous storage capacity in a slim fit
Dual evaporator	Our unique and efficient design separately cools the refrigerator while maintaining zero degrees in the freezer with two evaporators
Zero degree freezer	Stable interior allows you to store sensitive items under reliable freezer conditions
Cycle defrost	This system utilizes user-friendly automatic defrost operation in the fresh food section and efficient manual defrost operation in the freezer compartment
Adjustable thermostat	Dial thermostat located inside for easy temperature management
Interior light	Automatically illuminates when you open the door
Adjustable shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Crisper	Get the longest life and best taste out of produce by storing it in a convenient slide drawer
Door storage	Store tall bottles and condiments right on the door for easy access

CT66J Specifications:

Overview	
Height	33.25"
Height to Hinge Cap	33.5"
Width	23.63"
Depth	23.5"
Depth with door at 90°	45.13"
Capacity	5.1 cu.ft.
Defrost Type	Cycle
Door	White
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	102.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Yes
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Refrigerator - Interior Height	19.5"
Refrigerator - Interior Width	20.5"
Refrigerator - Interior Depth	17.0"
Refrigerator - Shelf Type	Wire
Refrigerator - Shelf Qty	2
Refrigerator - Full Door Shelves	3
Freezer - Interior Height	5.0"
Freezer - Interior Width	19.0"
Freezer - Interior Depth	11.5"
Adjustable Shelves	Yes
Interior Light	Yes
Thermostat Type	Dial
Freon	R134a
Freon Amount	2.6

High Side PSI	285.0
Low Side PSI	70.0
Level Legs	2
Compressor Step Height	7.0"
Compressor Step Width	20.5"
Compressor Step Depth	5.0"

