

# CT66LSSTB



33.5" x 23.63" x 23.5" (H x W x D)

Freestanding refrigerator-freezer for general purpose use, with lock, dual evaporator cooling, cycle defrost, SS door, towel bar handle and white cabinet

## Highlights:

Over 5 cu.ft. of storage capacity in a perfectly sized 24" footprint

Factory installed lock provides security you can count on

Stainless steel door includes curved towel bar handle for added luxury

Improved temperature performance with our unique dual evaporator cooling

## Product Features:

Slim counter height dimensions	Ideal 24" footprint offers full 5.1 cu.ft. storage capacity in a slim fit
Fully finished white cabinet	Allows the unit to be used freestanding
Stainless steel door	Durable design with lasting elegance
Professional towel bar handle	Curved handle in brushed stainless steel offers a sturdy grip with professional elegance
Factory installed lock	Keyed lock offers added security
Cycle defrost	This system utilizes user-friendly automatic defrost operation in the fresh food section and efficient manual defrost operation in the freezer compartment
Dual evaporator cooling	Our unique and efficient design separately cools the refrigerator while maintaining zero degrees in the freezer with two evaporators
Zero degree freezer	Stable interior allows you to store sensitive items under reliable freezer conditions
Adjustable shelves	Rearrange the refrigerator space to fit any sized item or remove shelves for simple cleanup

**CT66LSSTB Specifications:**

<b>Overview</b>	
Height	33.5"
Width	23.63"
Depth	23.5"
Depth with Handle	25.63"
Depth with door at 90°	45.63"
Capacity	5.1 cu.ft.
Defrost Type	Cycle
Door	Stainless Steel
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	113.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
<b>Refrigerator-Freezer</b>	
Door Swing	RHD
Reversible	Factory Reversible
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Refrigerator - Interior Height	19.5"
Refrigerator - Interior Width	20.5"
Refrigerator - Interior Depth	17.0"
Refrigerator - Shelf Type	Wire
Refrigerator - Shelf Qty	2
Refrigerator - Full Door Shelves	3
Freezer - Interior Height	5.0"
Freezer - Interior Width	19.0"
Freezer - Interior Depth	11.5"
Adjustable Shelves	Yes
Interior Light	Yes
Thermostat Type	Dial

Freon	R134a
Freon Amount	2.6
High Side PSI	285.0
Low Side PSI	70.0
Level Legs	2
Compressor Step Height	7.0"
Compressor Step Width	20.5"
Compressor Step Depth	5.0"

