



# FF1532BSS



34" x 14.75" x 22.75" (H x W x D)

15" wide all-refrigerator for built-in or freestanding use, with reversible stainless steel door and lock; replaces FF1538BSS

### Highlights:

Just under 15" wide for an easy fit, with a flush back design to save space

Flexible design allows built-in or freestanding use under counters

Reversible stainless steel wrapped door includes pro handle

Digital thermostat offers precise and convenient temperature control

### Product Features:

Built-in capable	Make the best use of space by installing your appliance under the counter
Fully finished black cabinet	Allows the unit to be used freestanding
Stainless steel door	Wrapped stainless steel door offers a professional look with lasting durability
Factory installed lock	Keyed security on the door
Digital thermostat	Electronic controls for precise temperature management.
Digital display	Temperature readout can be shown in Celsius or Fahrenheit
LED lighting	Gentle illumination with an on/off switch
Automatic defrost	No-frost operation ensures reduced maintenance
Adjustable glass shelves	Rearrange refrigerator space to accommodate all sizes or remove shelves for simple cleanup



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799

info@summitappliance.com




www.summitappliance.com



## FF1532BSS Specifications:

Overview	
Height	34.0"
Width	14.75"
Depth	22.75"
Depth with door at 90°	36.25"
Capacity	3.0 cu.ft.
Defrost Type	Frost-Free
Door	Stainless Steel
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Energy Usage/Year	255.0kWh/year
Amps	1.4
Voltage/Frequency	115 V AC/60 Hz
Weight	73.0 lbs.
Shipping Weight	83.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Shelf Type	Glass
Shelf Qty	3
Full Door Shelf Qty	2
Adjustable Shelves	Yes
Thermostat Type	Digital
Fan Type	Interior and Exterior
Refrigerant Type	R600a
Refrigerant Amount	0.64
High Side PSI	270.0
Low Side PSI	105.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	24.63"
Interior Width	12.0"
Interior Depth	17.63"

Compressor Step Height	3.13"
Compressor Step Width	12.0"
Compressor Step Depth	5.25"



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799 info@summitappliance.com www.summitappliance.com

