



FF64BCSS



34" x 23.63" x 23.5" (H x W x D)

Built-in undercounter all-refrigerator for residential or commercial use, frost-free w/stainless steel exterior, lock, and digital thermostat

Highlights:

Flexible design allows built-in or freestanding use in 24" wide spaces

Stainless steel door and wrapped cabinet offer a professional look

Recessed LED lighting offers attractive presentation of stored products

Factory installed lock provides security you can count on



Product Features:

ENERGY STAR certified commercial performance	Meets ENERGY STAR standards as a commercial refrigerator and meets DOE standards for residential use
Built-in capable	Front-breathing design lets you make the best use of space by installing your appliance under the counter
Stainless steel wrapped exterior	Cabinet is fully wrapped in durable 304 grade stainless steel
Fully finished cabinet	Allows the unit to be used freestanding
Stainless steel door	Durable construction with a professional look
Factory installed lock	Keyed lock for a secure interior
Professional handle	Includes a full-length pro handle in chrome
Frost-free operation	No-frost operation for minimum user maintenance
Digital thermostat	Electronic controls located inside the unit for precise temperature management



FF64BCSS Specifications:

Overview	
Height	34.0"
Width	23.63"
Depth	23.5"
Depth with Handle	25.38"
Depth with door at 90°	45.63"
Capacity	4.6 cu.ft.
Defrost Type	Frost-Free
Door	Stainless Steel
Cabinet	Stainless Steel
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Energy Usage/Year	250.0kWh/year
Amps	0.8
Voltage/Frequency	115 V AC/60 Hz
Weight	111.0 lbs.
Shipping Weight	120.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Shelf Type	Glass
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Digital
Fan Type	Interior and Exterior
Refrigerant Type	R600a
Refrigerant Amount	0.99oz.
High Side PSI	270.0
Low Side PSI	105.0
Interior Light	Yes
Dimensions	
Interior Height	24.0"
Interior Width	19.25"
Interior Depth	16.0"



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799

info@summitappliance.com

www.summitappliance.com