

FF6L7



33.5" x 23.63" x 23.5" (H x W x D)

Commercially listed freestanding all-refrigerator for general purpose use, with front lock, automatic defrost operation and white exterior

Highlights:

ENERGY STAR certified commercial refrigerator

Commercially approved for use in foodservice establishments

Factory-installed lock provides security you can count on

Full 5.5 cu.ft. capacity inside a convenient 24" footprint

Product Features:

ENERGY STAR certified commercial performance	Meets ENERGY STAR standards as a commercial refrigerator
Slim counterheight dimensions	Our unique 24" wide models offer full capacity in a slim fit
Commercially approved	ETL-S listed to NSF-7 commercial standards
Fully finished white cabinet	Allows the unit to be used freestanding
Front-mounted lock	Keyed lock offers added security
Automatic defrost	Reduced maintenance with auto defrost system
Hidden evaporator	Cold wall design with hidden evaporator and seamless interior
One piece interior liner	Enjoy easy clean-up with a seamless liner that won't hold a mess in hidden crevices
Adjustable shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up

FF6L7 Specifications:

Overview	
Height	33.5"
Width	23.63"
Depth	23.5"
Depth with Handle	25.13"
Depth with door at 90°	46.13"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	White
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Shipping Weight	102.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Crisper Qty	1
Crisper Finish	Opaque
Crisper Cover	Glass
Shelf Type	Wire
Shelf Qty	3
Full Door Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	2
Interior Light	Yes
Dimensions	
Interior Height	27.75"
Interior Width	20.0"
Interior Depth	17.5"
Compressor Step Height	7.0"

Compressor Step Width	20.0"
Compressor Step Depth	6.0"

