

FF7LBLADA



32" x 23.63" x 23.5" (H x W x D)

ADA compliant commercial all-refrigerator for freestanding general purpose use, with lock, auto defrost operation and black exterior

Highlights:

ENERGY STAR certified commercial refrigerator

Commercially approved for use in foodservice establishments

32" height for use in ADA compliant settings

Factory-installed lock provides security you can count on

Product Features:

ENERGY STAR certified commercial performance	Meets ENERGY STAR standards as a commercial refrigerator
Commercially approved	ETL-S listed to NSF-7 Standards for use in commercial establishments
ADA compliant	32" height for use in settings complying with ADA guidelines for lower counter height
Slim counter height dimensions	Less than 24 inches wide with a full 5.5 c.f. capacity
Factory installed lock	Keyed lock for a secure interior
Fully finished black cabinet	Allows the unit to be used freestanding
Reversible door	User-reversible door swing for added flexibility
Automatic defrost	Reduced user maintenance with automatic defrost
One piece interior liner	Easy clean-up with a seamless liner that won't hold a mess in hidden crevices

FF7LBLADA Specifications:

Overview	
Height	32.0"
Height to Hinge Cap	32.25"
Width	23.63"
Depth	23.5"
Depth with Handle	24.0"
Depth with door at 90°	45.13"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Black
Cabinet	Black
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	107.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Shelf Type	Glass
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	88.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	26.25"
Interior Width	21.0"
Interior Depth	17.75"
Compressor Step Height	5.5"
Compressor Step Width	21.0"

Compressor Step Depth

