

### Durable Design

- Stainless steel interior & exterior
- 3 height adjustable, heavy-duty, PE coated wire shelves per section
- LED interior lighting
- Digital temperature display
- Door locks with keys
- Simple plug-in installation

### Superior Quality

- Designed for mobility, reliability & efficiency in commercial kitchens
- Certified with ETL & Energy Star\*\* guaranteeing quality standards and energy efficiency
- 4" heavy duty, locking front casters
- Easy grip handle
- Entirely self-contained system
- Automatic defrost system
- Digitally controlled temperature system
- Accommodates full-size bun sheet pans
- Easily adjustable shelf height
- Internal storage capacity is 72 cu. ft.
- Holding temperature: Refrigerator 33°F to 39°F / Freezer 5°F to -9.4°F

### Energy Efficient

- Self-closing door with stay open feature
- Seals tight with magnetic vinyl gasket
- Open door alert beeps when door is open for 3 minutes
- Foamed-in place high-density polyurethane insulated body, CFC-Free
- Large evaporator & condenser for quick cooling and greater efficiency

## Triple Door Series Refrigerator & Freezer Bottom Mount Compressor KBSR-3 / KBSF-3



KBSR-3 / KBSF-3

Project Name:

Location:

Item:

Qty:




Model:



Tel.: 514.737.9701 / Toll Free: 888.275.4538  
Fax: 514.342.3854 / Toll Free: 877.453.8832  
sales@mvpgroupcorp.com • www.mvpgroupcorp.com



## TECHNICAL DRAWINGS KBSF-3 & KBSR-3



MODEL NUMBER	DESCRIPTION	INTERIOR / EXTERIOR MATERIALS	NUMBER OF DOORS	NUMBER OF SHELVES	CAPACITY (CUBIC FEET)	EXTERNAL DIMENSIONS (WxDxH in.) w/ handle	COMPRESSOR SIZE	VOLTAGE / FREQUENCY	AMPS	NEMA	REFRIGERANT	SHIP WEIGHT (lbs.)
KBSR-3	Bottom Mount Triple Door Refrigerator	Stainless Steel	3	9	72	81 x 32.75 x 82.7	5/8	115 V 60 Hz	10.3	5-15P	R134a	634
KBSF-3	Bottom Mount Triple Door Freezer	Stainless Steel	3	9	72	81 x 32.75 x 82.7	1	115 V / 208 -230 V 60 Hz	9.2A / 4.7A	L14-20P	R404a	650

These units are designed for maximum performance in an air-conditioned area of 75°F ambient temperature and 55% relative humidity. There must be adequate ventilation at the top, sides & rear of the unit for proper operation.



\*\* KBSF-3 Only

Warranty: 24 months parts & labor. Additional 36 months on compressor (parts only)

KOOL-IT is a registered trademark of MVP Group. Specifications subject to change without notice.



Tel.: 514.737.9701 / Toll Free: 888.275.4538  
Fax: 514.342.3854 / Toll Free: 877.453.8832  
sales@mvpgroupcorp.com • www.mvpgroupcorp.com