



Glass Door
Merchandiser Series
Refrigerators



**KGM-13
KGM-23**



KSM-36



**KSM-42
KSM-50**

Features

- Two-layer hollow glass, front side tempered, self-closing side-by-side or sliding door
- 4 universal wheels, 2 with brakes
- Black powder coated steel exterior and white painted aluminum interior
- LED Lighting
- Self-closing single and sliding doors
- Doors lock and key included
- Digital thermostat with LED display
- Auto-defrost

MODEL NUMBER	EXTERNAL DIMS (INCH) WxDxH	VOLTAGE / FREQUENCY	AMPS	STORAGE (CU-FT)	COMPRESSOR SIZE (HP)	TEMPERATURE	NET WEIGHT (LBS)	GROSS WEIGHT (LBS)	NEMA PLUG
KGM-13	22.6"x23.8"x77.9"	115V / 60 Hz	2.3	13	2/3	36°F - 43°F	161	176	5-15
KGM-23	27.6"x31.1"x81"	115V / 60 Hz	2.8	23	2/3	36°F - 43°F	234	269	5-15
KSM-36	44.5"x28.3"x79.5"	115V / 60 Hz	6.2	36	1	36°F - 43°F	342	386	5-15
KSM-42	52.4"x28.3"x79.5"	115V / 60 Hz	6.2	42	1	36°F - 43°F	348	430	5-15
KSM-50	52.4"x32.3"x79.5"	115V / 60 Hz	6.2	50	1	36°F - 43°F	401	463	5-15



Warranty : 12 months parts & labor. Additional 48 months on compressor (part only)

KOOL-IT is a registered trademark of MVP Group. Specifications subject to change without notice.



Tel.: 514.737.9701 / Toll Free: 888.275.4538
 Fax: 514.342.3854 / Toll Free: 877.453.8832
 sales@mvpgroupcorp.com • www.mvpgroupcorp.com