



# SBC635MBINKDPL



33.5" x 24" x 25.38" (H x W x D)

Built-in residential beer dispenser, auto defrost w/digital thermostat, diamond plate door, and TB handle; sold without tap kit for do-it-yourselfers

## Highlights:

Allows you to install your own custom tap equipment

Full-sized capacity to hold half, quarter, 1/6 or mini kegs

Designed for built-in installation under the counter

Textured diamond plate door in aluminum with polished towel bar handle offers an industrial look

## Product Features:

Full-sized beer dispenser	Large 5.6 cu.ft. interior can accept a full half barrel keg, two 1/6 barrel kegs, or a pony keg
Built-in capable	Make the best use of space by installing your appliance under the counter; NOTE: if installing flush with wall or cabinets, unit will require extra space due to the door design. Width should be 25" to 25 1/4". For more information, see the user manual
NO TAP KIT	Install your own tapping equipment for a customized beer cooler
Digital thermostat	Electronic controls ensure easy temperature management, with an external readout in Celsius or Fahrenheit
Ideal beer temperature	Operates between 33° and 50°F to keep a variety of beers stored at just the right serving temperature
Automatic defrost	Reduced maintenance with auto defrost system
Diamond plate door	Textured diamond plate finish in wrapped aluminum creates a unique industrial look
Professional towel bar handle	Curved handle in polished stainless steel completes the look
Fully finished black cabinet	Allows the unit to be used freestanding



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799



info@summitappliance.com



www.summitappliance.com



SBC635MBINKDPL Specifications:

Overview	
Height	33.5"
Width	24.0"
Width with Door Open	25.25"
Depth	25.38"
Depth with Handle	27.88"
Depth with door at 90°	47.0"
Capacity	5.6 cu.ft.
Dishwasher	Standard
Defrost Type	Automatic
Door	Diamond Plate
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Energy Usage/Year	310.0kWh/year
Amps	0.86
Voltage/Frequency	115 V AC/60 Hz
Weight	110.0 lbs.
Shipping Weight	140.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Beer Dispenser	
Door Swing	RHD
Reversible	Factory Reversible
Thermostat Type	Digital
Fan Type	Exterior
Refrigerant	R600a
Refrigerant Amount	1.13 oz.
High Side PSI	250.0
Low Side PSI	110.0
Inter Height	28.0"
Interior Width	20.5"
Interior Depth	19.0"
Compressor Step Height	8.25"
Level Legs Qty	4
Wheel Qty	4
Temperature Range	33° to 50° F

