



SBC635MBINKIF



33.5" x 24" x 25.38" (H x W x D)

Built-in beer dispenser, auto defrost w/digital thermostat and panel-ready door; sold without tap kit for do-it-yourselfers to install their own taps

Highlights:

Allows you to install your own custom tap equipment

Customizable door front accepts full overlay panels for a seamless look that can blend into cabinetry

Designed for built-in installation under the counter

Full-sized capacity to hold half, quarter, 1/6 or mini kegs

Product Features:

Full-sized beer dispenser	Large 5.6 cu.ft. interior can accept a full half barrel keg, two 1/6 barrel kegs, or a pony keg
Built-in capable	Make the best use of space by installing your appliance under the counter; NOTE: if installing flush with wall or cabinets, unit will require extra space due to the door design. Width should be 25" to 25 1/4". For more information, see the user manual
NO TAP KIT	Install your own tapping equipment for a customized beer cooler
Panel-ready door	Integrated stainless steel door frame accepts full overlay panels, allowing you to customize the door or blend it into your cabinetry design (panel dimensions: 23 3/4" W x 30 13/16" H and at least 3/4" thick)
Digital thermostat	Electronic controls ensure easy temperature management, with an external readout in Celsius or Fahrenheit
Ideal beer temperature	Operates between 33° and 50°F to keep a variety of beers stored at just the right serving temperature
Automatic defrost	Reduced maintenance with auto defrost system
Fully finished black cabinet	Allows the unit to be used freestanding
Reversible door	Use reversible door swing for added flexibility



SBC635MBINKIF Specifications:

Overview	
Height	33.5"
Width	24.0"
Width with Door Open	25.25"
Depth	25.38"
Depth with door at 90°	47.0"
Capacity	5.6 cu.ft.
Defrost Type	Automatic
Door	Panel-Ready
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Energy Usage/Year	310.0kWh/year
Amps	0.86
Voltage/Frequency	115 V AC/60 Hz
Weight	100.0 lbs.
Shipping Weight	130.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Beer Dispenser	
Door Swing	RHD
Reversible	Yes
Thermostat Type	Digital
Fan Type	Exterior
Refrigerant	R600a
Refrigerant Amount	1.13 oz.
High Side PSI	250.0
Low Side PSI	110.0
Inter Height	28.0"
Interior Width	20.5"
Interior Depth	19.0"
Compressor Step Height	8.25"
Level Legs Qty	4
Wheel Qty	4
Temperature Range	33° to 50° F



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799 info@summitappliance.com  www.summitappliance.com