



SBC635MBISSHH



33.5" x 24" x 25.38" (H x W x D)

Built-in residential beer dispenser, auto defrost with digital thermostat, stainless steel door, horizontal handle, and black cabinet

Highlights:

Full-sized capacity to hold half, quarter, 1/6 or mini kegs

Designed for built-in installation under the counter

Stainless steel door complete with sleek handle adds modern elegance to any setting

Includes everything you need to pour the perfect draft

Product Features:

Full-sized beer dispenser	Large 5.6 cu.ft. interior can accept a full half barrel keg, two 1/6 barrel kegs, or a pony keg
Built-in capable	Make the best use of space by installing your appliance under the counter; NOTE: if installing flush with wall or cabinets, unit will require extra space due to the door design. Width should be 25" to 25 1/4". For more information, see the user manual
Tap Kit	Includes a 5 lb. CO2 tank and regulator, draft arm, Sankey American tap, and connection hardware
Stainless steel wrapped door	Durable design with lasting elegance
Professional horizontal handle	Brushed stainless steel handle with a thin 14mm diameter is mounted horizontally across the door for a sleek look
Automatic defrost	Reduced user maintenance with auto defrost operation
Digital thermostat	Electronic controls ensure easy temperature management, with an external readout in Celsius or Fahrenheit
Ideal beer temperature	Operates between 33° and 50°F to keep a variety of beers stored at just the right serving temperature

Fully finished black cabinet

Allows the unit to be used freestanding



SBC635MBISSHH Specifications:

Overview	
Height	33.5"
Width	24.0"
Width with Door Open	25.25"
Depth	25.38"
Depth with door at 90°	47.0"
Capacity	5.6 cu.ft.
Defrost Type	Automatic
Door	Stainless Steel
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Energy Usage/Year	310.0kWh/year
Amps	0.86
Voltage/Frequency	115 V AC/60 Hz
Weight	110.0 lbs.
Shipping Weight	140.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Beer Dispenser	
Door Swing	RHD
Reversible	Yes
Tap Kit	Yes
Number of Taps	1
Thermostat Type	Digital
Fan Type	Exterior
Refrigerant	R600a
Refrigerant Amount	1.13 oz.
High Side PSI	250.0
Low Side PSI	110.0
Inter Height	28.0"
Interior Width	20.5"
Interior Depth	19.0"
Compressor Step Height	8.25"
Level Legs Qty	4
Wheel Qty	4
Temperature Range	33° to 50° F



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799 info@summitappliance.com  www.summitappliance.com