



SPR6270SCSSTB



34" x 23.63" x 23.5" (H x W x D)

Outdoor all-refrigerator for built-in use, with lock, digital thermostat, towel bar handle, and stainless steel wrapped exterior

Highlights:

ENERGY STAR certified commercial refrigerator

Designed and constructed for use in the outdoors

Flexible design allows built-in or freestanding use in 24" wide spaces

Recessed LED lighting offers attractive presentation of stored products

Product Features:

ENERGY STAR certified commercial performance	Meets ENERGY STAR standards as a commercial refrigerator and meets DOE standards for residential use
Built-in capable	Front-breathing design lets you make the best use of space by installing your appliance under the counter
Stainless steel cabinet	Wrapped cabinet allows durable use in the outdoors
Stainless steel wrapped door	Durable construction with a professional look
Professional handle	Curved handle in brushed stainless steel
Factory installed lock	Keyed lock for a secure interior
Frost-free operation	No-frost operation for minimum user maintenance
Digital thermostat	Electronic controls located inside the unit for precise temperature management
Recessed LED light	Elegant lighting with a convenient on/off switch on the control panel



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799

info@summitappliance.com

www.summitappliance.com



SPR627OSCSSTB Specifications:

Overview	
Height	34.0"
Width	23.63"
Depth	23.5"
Depth with Handle	25.38"
Depth with door at 90°	45.63"
Capacity	4.6 cu.ft.
Defrost Type	Frost-Free
Door	Stainless Steel
Cabinet	Stainless Steel
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Energy Usage/Year	250.0kWh/year
Amps	0.8
Voltage/Frequency	115 V AC/60 Hz
Weight	110.0 lbs.
Shipping Weight	120.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Shelf Type	Glass
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Digital
Fan Type	Interior and Exterior
Refrigerant Type	R600a
Refrigerant Amount	0.99
High Side PSI	270.0
Low Side PSI	105.0
Interior Light	Yes
Dimensions	
Interior Height	24.0"
Interior Width	19.25"



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799

✉ info@summitappliance.com



www.summitappliance.com