

DESCRIPTION

The CCE Series offers quality and value with a compact and attractive Thin Die-Cast aluminum Exit sign. Exit face illumination by low energy, long-life red or green ultra bright LED's. The Exit face-plate is brushed aluminum with black edges and 6" letters with a red or green diffuser. Single-face models can be wall, end or ceiling mounted. Double-face models are end or ceiling mounted only. Includes canopy and universal mounting plate. Test switch and AC-on indicator located at bottom center. Directional indication made by knock-out chevrons. Available with battery for emergency operation or AC only.

APPLICATION

The CCE Series can be applied in stair-wells, hallways, offices and other commercial applications.

COMPLIANCES

UL924 Listed for Damp Location
NFPA 101 and NFPA 70
OSHA

WARRANTY

2 year full unit warranty

ENERGY CONSUMPTION

120 VAC	277 VAC
1 W	1 W




FEATURES

- LED life-cycle of more than 10 years
- Molded-in template for Quick installation
- Dual-voltage 120 or 277V AC input
- Emergency models include long-life 2.4VDC Nickel Cadmium battery for UL recognized 90 minute operation
- Damp Location Listed(0° to 50°C)
- Provided with test switch and AC-On indicator
- Canopy Included
- 24hr. Re-charge

ORDERING GUIDE

Catalog Number	Description
CCESRE	Brushed Face, Black Housing, Single-Face, Red, Emergency
CCEDRE	Brushed Face, Black Housing, Double-Face, Red, Emergency
CCESGE	Brushed Face, Black Housing, Single-Face, Green, Emergency
CCEDGE	Brushed Face, Black Housing, Double-Face, Green, Emergency
CCESR	Brushed Face, Black Housing, Single-Face, Red, AC
CCEDR	Brushed Face, Black Housing, Double-Face, Red, AC
CCESG	Brushed Face, Black Housing, Single-Face, Green, AC
CCEDG	Brushed Face, Black Housing, Double-Face, Green, AC

DIMENSIONS



Single Carton Weight: 2.8 lbs.
Master Carton Quantity: 8 each