

# J-3130, 5" X 8" HORIZONTAL BANDSAW

414461

Adjustable guides and hydraulic feed, steel worm gear and bronze drive gear, and auto shutoff at end of the cut are some of the features that makes this JET Hydraulic Band Saw a must for any professional machine shop. The built-in handle and wheels makes relocation within your workspace quick and easy.



## FEATURES

- For added safety, the J-3130 follows strict guidelines and electrical requirements to be certified by CSA Group
- Blade drive is a steel, heat treated worm driving a bronze worm gear in an oil bath
- Adjustable blade guides with side eccentric shaft with ball bearings with rear-ball bearings
- Fully adjustable hydraulic downfeed system
- Wheels and handle for easy movement
- Adjustable material stop
- 1/2" Carbon Steel Blade



## JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

# J-3130, 5" X 8" HORIZONTAL BANDSAW

414461

## SPECIFICATIONS

Cutting Capacity (W x D) (In.)	5 x 8
Round at 90 Degrees (In.)	5
Round at 45 Degrees (In.)	4-1/2
Rectangle at 90 Degrees (In.)	7-1/2 x 5
Rectangle at 45 Degrees (In.)	4-1/2 x 5
Vise Swivels (Deg.)	45°
Blade Speeds (SFPM)	85, 125, 200
Blade Wheel Diameter (In.)	7-1/2
Blade Length (In.)	68-1/2
Blade Size (In.)	1/2 x .025 x 68
Bed Height (In.)	23-1/2
Motor (HP)	1/2 HP, 115V, 1Ph
Weight (Lbs.)	134
Overall Dimensions (L x W x H) (In.)	37 x 16 x 37



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE