

SR-2024M, 24" X 20 GAUGE BENCH MODEL SLIP ROLL

756020

JET manual slip rolls have a forming width of 24", 36" & 50" with a capacity of 20, 22 & 16 gauge mild steel. These machines have two driven rolls of precision turned, ground and polished carbon steel. They are the perfect sheet metal forming machines to have in any general fabrication, school, racing or HVAC shop. The highly rigid construction frame ensures precision roll bending for decades of production. This sheet metal roller comes standard with three wire or rod grooves.



FEATURES

- Perfect tool for sheet metal forming in HVAC and FAB-shops
- Suitable for many industrial, educational and vocational shop uses
- Precision turned carbon steel rolls that are ground and polished
- Large roll adjusting screws facilitate lifting upper roll for easy material removal
- Wire grooves are standard on SR-2024N, SR-2236N and SR-1650N



JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

SR-2024M, 24" X 20 GAUGE BENCH MODEL SLIP ROLL

756020

SPECIFICATIONS

Mild Steel Capacity (Gauge)	20
Maximum Forming Length (In.)	24
Number and Diameter of Rolls (In.)	3, 2
Minimum Forming Radius (In.)	1
Wire Grooves (In.)	3/16, 1/4, 5/16
Overall Dimensions (L x W x H) (In.)	50 x 14 x 14
Weight (Lbs.)	216



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE