



# HydroPlug™

## Patch and repair active leaks in 3 – 5 minutes

### Repair Thickness

¾" to 3"

### Set Time

3 to 5 minutes

### Application Technique

Trowel, Gloved Hand

### Where to Use

- Stop active leaks
- Fill holes
- Anchor equipment and machinery
- Concrete patching
- Seal cracks
- Elevator pits, wells

### Features

- Easy to mix and finish
- Long lasting formula
- Highly versatile
- Excellent compressive strengths
- Extra rich for smooth troweling
- Very short setting time
- Mix with water or latex liquid

### Packaging and Yield

3 lb, 10 lb, 48 lb units

### Product Description

**HydroPlug** is a special blend of cement, aggregates, accelerating additives and other modifiers. **HydroPlug** offers the ultimate in workability. Designed to be applied with a gloved hand or trowel in one or more applications. Used to quickly patch holes, repair active leaks, and to anchor machinery and equipment.

### For Best Results

Apply to a clean, dry sound substrate above 40° F. Cracks or holes must be opened to a minimum width of ¾". Do not retemper already mixed material. Do not expose to rain or flowing water during application. If repairing an active leak, hold product securely in place until firmly set. Store in a cool, dry area in strict accordance with manufacturer's recommendations.

### Surface Preparation

Surface preparation is critical to achieve long lasting results. Existing concrete surface shall be clean, sound, and free of oil, grease, laitance, curing compounds, or any other foreign substance. Areas treated with product must be free of dust and any foreign matter prior to topping application. On highly porous substrates, contact the manufacturer for recommended application procedures.

### Mixing Guidelines

Always add powder into water or latex. For faster set time, mix with clean lukewarm water. For increased bond strength, mix with latex liquid. A putty-like consistency is recommended.

### Application

Apply with gloved hand or trowel to clean, sound and stable substrates only. Cracks or holes must be opened a minimum of ¾" wide. Wait for leaking water to stop or reach its lowest ebb, then place mixed material with trowel edge onto surface and hold in place until firmly set.

### Curing

Sets in 3 to 5 minutes at 70° F. Avoid applications in high winds, excessive heat or blowing air directly on freshly placed product. Contact JE Tomes if you have any questions or concerns with your application.

### Warning

**KEEP OUT OF REACH OF CHILDREN.** If eaten or swallowed, serious personal injury could occur. Prolonged contact with skin may cause irritation. In case of eye contact, flood eyes repeatedly with water. Consult your physician under any of the above circumstances.

### LIMITED WARRANTY

JE Tomes & Associates, Inc. warrants its products to be free from manufacturing defects and will deliver, at no charge, an equal amount of packaged product as that amount proven to be defective when applied in accordance with manufacturer's written directions by contractors experienced in this application, and used in applications recommended by the manufacturer as suitable for the product. All claims concerning product defects must be made within twelve (12) months of use of the product. THERE ARE NO OTHER WARRANTIES BY JE TOMES & ASSOCIATES, INC. OF ANY NATURE WHATSOEVER, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE IN CONNECTION WITH PRODUCTS WHICH EXTEND BEYOND THE DESCRIPTION ON THE FACE HEREOF. Buyer's sole and exclusive remedy for breach of any warranty shall be replacement of defective product. JE Tomes & Associates, Inc. shall not be liable for any damages, including consequential damages, except as otherwise set forth therein.