

Made in the USA by JE Tomes, an American Owned and Operated Company

2513 W. 140th Place • Blue Island, IL 60406

# **JETaFLOW**<sup>™</sup>

## Self leveling mortar for applications up to 1" thick

**Repair Thickness** Featheredge to 1"

Set Time 1 hour

Application Technique Pour, Pump

#### Where to Use

- Unleveled concrete
- As an underlayment
- As a wear surface
- Interior or exterior surfaces
- Warehouse floors
- With radiant heat flooring
- Decorative flooring

#### Features

- Heavy duty Over 6000 psi
- One component—Just add water
- No troweling—Self leveling
- Portland cement based
- Polymer modified
- Pumpable
- Short wait for foot traffic

#### **Packaging and Yield**

50 lb heavy duty polyethylene bag 50 sq ft at 1/8"

#### **Product Description**

**JETAFLOW** is a heavy duty 1 component polymer modified self-leveling underlayment, concrete repair, and resurfacing mortar. **JETAFLOW** is simply mixed with water and applied from featheredge to 1" thick in one application. Product is ready for light traffic in 4 to 5 hours at 70° F.

**JETAFLOW** is a special blend of cements, aggregates and exclusive modifiers. Designed for general purpose and high performance underlayment, concrete repair or resurfacing applications.

#### **For Best Results**

Apply to a clean, dry sound substrate above 40° F. For all uses, apply primer to surface before application. Check moisture content (mat test) prior to applying any waterproof topping. Do not retemper already mixed material. On highly porous substrates and wood substrates, contact the manufacturer for recommended application procedures.

#### **Surface Preparation**

Surface preparation is critical. Existing surface should be clean, sound, and free of oils, curing compounds, dust or any other foreign matter. Preparing surface by mechanical means such as grinding or shot blasting is recommended. Priming the surface is necessary to self level. Broom **JETaFLOW Primer** onto sub-floor, making sure not to puddle primer. Apply **JETaFLOW** after **JETaFLOW Primer** dries clear (1 to 2 hours in normal conditions). For extremely porous surfaces, 2 coats of primer may be required.

#### **Mixing Guidelines**

Approximately 5 to 5 ½ quarts of water are required to mix 50 lb of product. Using a paddle mixer, always add and mix product into water. Mix for no less than 3 minutes.

#### Application

Pour **JETaFLOW** onto the primed surface. To break surface tension a porcupine roller is recommended. For large area applications it is recommended to start near the perimeter in a continuous operation using a long handle spreader to distribute the product where needed. For patching application, pour material into primed area to level. For applications over 1" use **JETaFLOW High Build**. Apply to primed, clean sound substrates only. Contact JE Tomes for any questions.

#### Curing

Rapid drying of cement-based products may cause cracking or de-bonding. Avoid applications in high winds, excessive heat or blowing air directly on freshly placed product. Contact JE Tomes if you have any questions or particular concerns with your application.



Made in the USA by JE Tomes, an American Owned and Operated Company

For concrete repair and restoration

2513 W. 140th Place • Blue Island, IL 60406

# JETaFLOW™

### **Technical Data**

Compressive strength, 28 day	Exceeds 6000 psi	ASTM C109
Compressive strength, 7 day	Exceeds 3000 psi	ASTM C109
Compressive strength, 1 day	Exceeds 2500 psi	ASTM C109
Flexural strength, 28 day	Exceeds 800 psi	ASTM C78
Freeze/thaw durability	Excellent	ASTM C666
Bond strength	Exceeds 150 psi	ACI 503 R
Color	Concrete gray	

Reasonable variations for the above data can be expected depending on field conditions, surface preparation, curing, contractor expertise and evaluation and/or handling of test cylinders. Contact JE Tomes for additional details.

#### LIMITED WARRANTY

JE Tomes & Associates, Inc. warrants its products to be free from manufacturing defects and will deliver, at no charge, an equal amount of packaged product as that amount proven to be defective when applied in accordance with manufacturer's written directions by contractors experienced in this application, and used in applications recommended by the manufacturer as suitable for the product. All claims concerning product defects must be made within twelve (12) months of use of the product. THERE ARE NO OTHER WARRANTIES BY JE TOMES & ASSOCIATES, INC. OF ANY NATURE WHATSOEVER, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE IN CONNECTION WITH PRODUCTS WHICH EXTEND BEYOND THE DESCRIPTION ON THE FACE HEREOF. Buyer's sole and exclusive remedy for breach of any warranty shall be replacement of defective product. JE Tomes & Associates, Inc. shall not be liable for any damages, including consequential damages, except as otherwise set forth therein.