

LV11 Heat-Only Mecahnical Thermostat

Single-Pole Line-Voltage

Heat-Only Mechanical

Product Highlights

- ✓ Easy to use
- ✓ Mercury free
- √ 5 year warranty
- ✓ Single-Pole Line-Voltage



Product Features

- Easy to install and use
- Clean attractive design
- Contains no mercury
- ETL certified (USA, Canada)
- Single bi-metallic temperature sensing strip
- 5 year warranty

Thermostat Electrical Ratings:

- Resistive: 22A at 120/208/240/277 VAC (2640W @ 120V, 5280W @ 240V)
- Inductive: 1/2 HP @ 120V, 3/4 HP @ 240V

Physical Dimensions (When Mounted):

- Width = 2.75" (70 mm)
- Height = 4.50" (115mm)
- Depth = 1.50" (40mm)

Installation

Compatible With

■ 1-stage heat only: single-pole (2-wires) and 120/240 VAC systems up to 22 amps

Not Compatible With

- Conventional 24V heating applications
- Millivolt heating applications
- Cooling applications

Carton Pack Quantity:

■ 5 pieces

UPC Code:

0 21079 14262 0

